




WARNING KITS

219 EMERGENCY WARNING TRIANGLE KIT



- Meets/exceeds all DOT FMVSS125 Requirements
- Triangle's wire form support guarantees tilt compliance of 40 mph wind test
- Opaque container protects fluorescent color from UV deterioration
- Unique living hinge box, wire support and tabs are available ONLY by Cortina
- Living hinge box ensures the lid will not separate from the box
- Weighted base ensures triangles will not move by wind gusts caused by passing traffic

| ITEM # | DESCRIPTION |
|-----------|--|
| 95-03-009 | Three (3) triangles in Living Hinge Box - 1/pack |
| 95-03-010 | Three (3) triangles in Living Hinge Box - 4/pack |

319 EMERGENCY WARNING TRIANGLE KIT WITH HANDLE



- Meets/exceeds all DOT FMVSS125 Requirements
- Triangle's wire form support guarantees tilt compliance of 40 mph wind test
- Opaque container protects fluorescent color from UV deterioration
- Unique living hinge box, wire support and tabs are available ONLY by Cortina
- Living hinge box ensures the lid will not separate from the box
- Weighted base ensures triangles will not move by wind gusts caused by passing traffic

| ITEM # | DESCRIPTION |
|--------------|--|
| 95-02-002-03 | Three (3) triangles in Plastic Box with Handle |

FLEET EMERGENCY KIT



- Meets/exceeds all DOT FMVSS125 Requirements
- Triangle's wire form support guarantees tilt compliance of 40 mph wind test
- Weighted base ensures triangles will not move by wind gusts caused by passing traffic

| ITEM # | DESCRIPTION |
|--------------|--|
| 95-04-001-02 | Fleet safety kit w light sticks |
| 95-04-002 | Fleet safety kit w/o fire extinguisher |
| 95-04-004 | Fleet safety kit 2 3/4 lb. fire extinguisher w bracket |

INDIVIDUAL REFLECTIVE TRIANGLE KIT



- Meets/exceeds all DOT FMVSS125 Requirements
- Triangle's wire form support guarantees tilt compliance of 40 mph wind test
- Opaque container protects fluorescent color from UV deterioration
- Unique living hinge box, wire support and tabs are available ONLY by Cortina
- Living hinge box ensures the lid will not separate from the box
- Weighted base ensures triangles will not move by wind gusts caused by passing traffic

| ITEM # | DESCRIPTION |
|--------------|------------------------------------|
| 95-02-001 | Single (1) triangle flare |
| 95-02-002-01 | Single (1) triangle in plastic box |
| 95-02-002-02 | Two (2) triangles in plastic box |





CONES & ACCESSORIES

DW SERIES TRAFFIC CONES

- Wide body design
- Injection molded PVC
- Black rugged base
- Meets NCHRP-350 Certification
- Meets MUTCD Standards
- Custom imprinting available



| ITEM # | DESCRIPTION | WT |
|-------------|-------------------------------|--------|
| 03-500-07 | 28" Plain Orange | 7 lbs |
| 03-500-18 | 28" Plain Orange | 10 lbs |
| 03-500-10 | 28" Orange 6" / 4" Collars | 7 lbs |
| 03-500-103M | 28" Orange 6" / 4" 3M Collars | 7 lbs |
| 03-500-24 | 28" Orange 6" / 4" Collars | 10 lbs |
| 03-500-243M | 28" Orange 6" / 4" 3M Collars | 10 lbs |
| 03-500-063M | 36" Orange 6" / 4" 3M Collars | 10 lbs |
| 03-500-06 | 36" Orange 6" / 4" Collars | 10 lbs |

CONE HOLDER

- Holds no more than (1) 18" cones or (5) 28" cones
- Mounting plate is 6.75" wide
- Height of unit = 22" from bottom of mounting plate to top of holder
- Hardware not included

| ITEM # | DESCRIPTION |
|-----------|-----------------------|
| 03-500-99 | 22" Steel Cone Holder |



WARNING LIGHTS

TEAR DROP LIGHTS



- Meets / exceeds SAE Requirements
- Industries highest quality and dependable Rotating Halogen Light
- Low Profile Tear Drop Light

| ITEM # | DESCRIPTION |
|----------|-------------|
| 22-56525 | Amber |
| 22-56526 | Red |
| 22-56527 | Blue |

PULSATOR LED



- Fourteen selectable flash patterns
- LED technology for 0 maintenance
- No bulbs or strobe tubes to replace
- Multi-voltage
- 12-24 VDC, Class 2, Five-year LED warranty

| ITEM # | DESCRIPTION |
|----------|--------------------|
| 22-56530 | Amber Perm Mount |
| 22-56531 | Amber Magnet Mount |

FIREBOLT LED



- Fourteen selectable flash patterns
- Polycarbonate dome & base
- Multi-voltage
- 12-24 VDC, Class 2, Five-year LED warranty

| ITEM # | DESCRIPTION |
|----------|--------------------|
| 22-56532 | Amber Magnet Mount |



WARNING LIGHTS

PULSATOR 451 LED



- Fourteen selectable flash patterns
- LED technology for 0 maintenance
- No bulbs or strobe tubes to replace
- Multi-voltage
- 12-24 VDC, Class 2, Five-year LED warranty

| ITEM # | DESCRIPTION |
|----------|------------------------|
| 22-56533 | Amber Short Perm Mount |

SENTRY



- 95 FPM
- Large parabolic reflector & 55-att Halogen bulb
- 80,000 candelas per flash
- Rugged Polycarbonate housing
- Twist off dome for easy maintenance
- Class 1 Five-year LED warranty

| ITEM # | DESCRIPTION |
|----------|---------------------|
| 22-56535 | 12 VDC Magnet Mount |

VISIBEAM II



- High power spotlight
- Graduated start for pinpoint light beam placement
- Continuous 360° horizontal and 140° vertical adjustment
- FCC approved
- Three-year warranty

| ITEM # | DESCRIPTION |
|----------|----------------------|
| 22-56537 | 12 VDC surface mount |

HIGHLIGHTER LED ECONOMY



- High output Solaris LED reflector technology
- ROC (Reliable Onboard Circuitry) - reduces potential failure points
- Low profile
- 2.6" tall, Class 1, Five-year warranty

| ITEM # | DESCRIPTION |
|----------|--------------------------------|
| 22-56540 | Amber Suction Cup Magnet Mount |
| 22-56541 | Amber Permanent Mount |

LATITUDE



- High output Solaris LED reflector technology
- ROC (Reliable Onboard Circuitry) - reduces potential failure points
- Ten flash patterns and one test pattern
- Polycarbonate, moisture resistant housing
- Class 1, Five-year LED warranty

| ITEM # | DESCRIPTION |
|----------|--|
| 22-56543 | Latitude LED Flashing, Amber 12-14 VDC, Surface Mount |
| 22-56545 | Latitude SignalMaster LED, Amber, 12-14 VDC, Surface Mount |





FLARE KITS

FLARE HOLDERS

- Designed to hold 20 or 30 minute fuseses
- Constructed from Heavy Duty Polypropylene
- Easy Grab handle and no roll design

| ITEM # | DESCRIPTION |
|-----------|--|
| 95-07-003 | Holder case 12/20 Minute |
| 95-07-004 | Holder case 12/30 Minute |
| 95-07-005 | Holder case w bracket 3/20 Minute & wire stand |
| 95-07-006 | Holder case w bracket 3/30 Minute |
| 95-07-007 | Holder case bracket w 3/30 Minute |



FLARES

- Available in 20 and 30 minute types
- Moisture resistant
- Spike or non-spike, or wire stand

| ITEM # | DESCRIPTION |
|----------|-------------------------------------|
| 95-07-20 | 20 Min Spike Type 72/case |
| 95-07-21 | 20 Min Flare w/o Spike 72/case |
| 95-07-22 | 20 Min Flare w Wire Stand - 72/case |
| 95-07-30 | 30 Min Flare Spike Type 36/case |
| 95-07-31 | 30 Min Flare w/o Spike 36/case |
| 95-07-32 | 30 Min Flare w Wire Stand - 36/case |



FLARE KITS



- Heavy Duty injection molded plastic boxes hold 4 or 12 minute fuseses
- Moisture resistant
- Compact design for tight storage space - fits conveniently under most seats

| ITEM # | DESCRIPTION |
|-----------|---------------------------|
| 95-07-001 | 4 Flares |
| 95-07-002 | 12 Flares and Safety Vest |

MOTORIST FLARE KITS



- For automotive after market and heavy duty markets
- 6-Pack flare configuration
- Bright Orange safety vest for flare deployment
- Storage case with flare pockets and vest holder
- Double zipped 600 Denier Polyester bag keeps flares together
- Velcro on back of bag secures placement in trunk or under seat

| ITEM # | DESCRIPTION |
|-----------|-----------------|
| 95-07-25G | 20 Minute Flare |
| 95-07-35G | 30 Minute Flare |

MOTORIST SAFETY KIT



- Meets/exceeds all DOT FMVSS125 Requirements
- Triangle's wire form support guarantees tilt compliance of 40 mph wind test
- Weighted base ensures triangles will not move by wind gusts caused by passing traffic

| ITEM # | DESCRIPTION |
|-----------|---------------------------|
| 95-02-001 | Single (1) Triangle Flare |



WWW.CORTINACO.COM

UNITED STATES 800.225.5206
WORKZONE@CORTINACO.COM

CANADA 866.757.1900
WORKZONECANADA@CORTINACO.COM

INTERNATIONAL 847.455.2800
WORKZONE@CORTINACO.COM / WORKZONECANADA@CORTINACO.COM

© 2017 CORTINA SAFETY PRODUCTS GROUP