

# Product data sheet

## Characteristics

# 8538SDG14V02S

Combination Starter, Type S, fusible disconnect, Size 2, 45A, 3 pole, 120 VAC coil, melting alloy overload, NEMA 1



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	45 A
Number of Poles	3P
Horsepower Rating	25 Hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 60 A
NEMA size	2
Height	22.50 in (571.50 mm)
Depth	9.59 in (243.59 mm)
Width	10.50 in (266.70 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
Product Certifications	UL Listed CSA

### Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	785901515531
Nbr. of units in pkg.	1
Package weight(Lbs)	44.75 lb(US) (20.298 kg)
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	12.00 in (30.48 cm)
Package 1 width	14.00 in (35.56 cm)
Package 1 Length	32.30 in (82.042 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------