


# Tools for Building, Construction, Engineering and Design Professionals



Model 8025

Easy-to-use to get the results that Pros rely on — over 400 unit conversion combinations. Reduce waste, improve design accuracy and cut estimating time.

## Enhanced Features and Built-in Functions Provide Problem Solving Benefits

- Get maximum conversion versatility and accuracy
- Extensive choice of measurement units and conversions
- Linear, Area, Volume, Weight, Weight to Volume
- Linear Velocity, Flow Rates, Pressure, Bending Moment, Temperature
- No formulas to remember, no complicated entry routines or protocol to follow



4840 Hytech Drive  
Carson City, NV 89706  
1-775-885-4900

Visit our website at:  
[www.calculated.com](http://www.calculated.com)

## ULTRA MEASURE MASTER®

MODEL 8025

Professional Grade U. S. Standard  
to Metric Conversion Calculator

An easy-to-use calculator that provides more than 400 conversion combinations utilizing 60 built-in Standard and Metric units. Easily calculate Linear, Area and Volume Measurements. Find Dry and Liquid Weights per Volume. Solve for Velocity, Flow Rate, Pressure and Temperature. Work in and convert between Feet-Inch-Fractions, Millimeters, Centimeters and Meters; PSI, GPM and more! No more time wasted with tables. Reduce costly mistakes!



Linear, Area, Volume, Weight



Weight to Volume



Linear Velocity, Flow Rates,  
Pressure, Bending Moment



Temperature Conversions

Ultra Measure Master is the choice for:



- Designers
- Engineers
- Excavation/Highway Contractors
- Contractors/Builders
- Purchasing
- Machinists
- Draftspersons
- Architects
- Importers/Exporters

### Product Specifications — Ultra Measure Master Model 8025

**Size:** 5.7" x 3.0" x 0.65" (145mm x 76mm x 17mm)  
**Weight:** 4.15 oz. (117.7 gm) does not include Pocket Reference Guide  
**Power:** Single 3-volt Lithium Battery (CR-2016)  
**Display:** 11 Digits\* (7 normal, 4 fractions) with Full Annunciators  
**LCD Dimensions:** 0.73" x 2.56" (19mm x 65mm)  
**Accuracy:** 12 Digit Internal Accuracy

\* Maximum Display: up to 19999999.99

**Included with Every Ultra Measure Master:**  
Protective Slide Cover; Long-life Battery (One CR-2016);  
Easy-to-follow User's Guide and handy Quick Reference Guide.

#### Full One-Year Limited Warranty:

All Calculated Industries calculators and electronic tools are covered by a Full One-Year Limited Warranty against defects in materials and workmanship. The full text of each warranty is published in the documentation accompanying each product and at [www.calculated.com](http://www.calculated.com). Calculated Industries reserves the right to make changes in the materials and specifications of products without notice.



**Protective Slide Cover**  
Slips on the front to protect the keys and the LCD or on the back when the calculator is in use.

# Fast, Accurate and Easy to Use!

## Dimensional Math and Conversions

- More than 60 Standard and Metric (SI) units built-in for fast, reliable conversions on the job or in the office.
- Over 400 conversion combinations.
- Works in and converts between Feet, Inches, Fractions, Yards, Meters, Centimeters, Millimeters, — including Square and Cubic formats.

## Dedicated Functions

- **Linear:** Feet-Inch-Fractions, Yards, Miles, Decimal Feet/Inch, Millimeters, Centimeters, Meters and Kilometers.
- **Area:** Feet, Inch, Yards, Acres, Miles, Millimeters, Centimeters, Meters, Hectares and Kilometers.
- **Volume:** Quickly find all U.S. Standard and Metric cubic volumes including Board Feet.
- **Weight:** Pounds, Dry Ounces, Tons, Metric Tons, Grams and Kilograms.
- **Weight per Volume:** Tons per Cubic Yard, Pounds per Cubic Yard, Kilograms per Cubic Meter and more.
- **Linear Velocity:** Inches and Feet per Second, Feet per Minute, Miles per Hour, Millimeters and Meters per Second/Minute and Kilometers per Hour.

- **Flow Rate:** Ounces per Second, Gallons per Minute, Milliliters and Liters per Second.
- **Pressure:** Pounds per Square Inch (PSI), Pounds per Square Foot (PSF), Kilopascal, Megapascal and Bars.
- **Bending Moment:** Inch-Pounds, Foot-Pounds and Newton-Meters.
- **Temperature:** Fahrenheit (°F) and Celsius (°C).

## Additional Features

- **User Preferences — set custom options:** Fractions, Area, Volume.
- **Cost per Unit:** Solve unit cost and pricing.
- **Backspace Key:** Easily correct entry errors.
- **“Paperless” Tape:** Allows review of the last 20 entries; double-check totals.
- **Standard Calculations:** Works as a standard math calculator with %, +, −, ×, ÷, +/−, 1/x, x<sup>x</sup> and  $\bar{x}$ .

# ULTRA MEASURE MASTER®

MODEL 8025

Professional Grade U. S. Standard to Metric Conversion Calculator

DESIGNERS • ENGINEERS • CONTRACTORS/BUILDERS • DRAFTSPERSONS • ARCHITECTS  
EXCAVATION/HIGHWAY CONTRACTORS • PURCHASING • MACHINISTS • IMPORTERS/EXPORTERS

**Over 400 of the most-needed unit conversion combinations!  
Dedicated Keys and Functions Make It Easy To Use**

