





Better Best





Diamond Flex-Lok™ is a high performance floor mat system that combines durability and toughness with true ergonomic support and comfort. The ergonomic properties are the result of a multi-tiered footing design that elevates the mat off the floor, creating air pockets that allow it to flex with the weight of the worker. A large hole drainage system facilitates the removal of liquids and debris from the work area. Made from a 100% recycled PVC compound, it offers the highest degree of resistance to many commonly found chemicals, oils, and greases. It's the perfect mat system for tough environments where custom configurations are a consideration.

Test	Test Description	*Results
N/A	Compression Deflection (The greater the deflection, the better the anti-fatigue properties)	@ 20 lbs/sq. in 0.371 @ 40 lbs/sq. in 0.435
N/A	Abrasion Resistance (Measured in weight loss)	Would not allow circular rotation of taber
ASTM C-1028	Static Coefficient of Friction	0.690
ASTM D-2240	Durometer / Hardness	Shore A - 85
ASTM E-648	Critical Radiant Flux	Class - 1

^{*}All testing of NoTrax* floor matting has been performed by an independent testing laboratory.



Drainage



Anti-Fatigue



industrial chemicals

• Solid PVC vinyl construction: highly resistant to

- 7/8" diameter large-hole perforations for easy drainage
- A unique interlock system that comes apart only when you want it to, allows for easy reconfiguration
- Made from 100% recycled PVC (black only)
- Overall thickness: 1"
- Sizes: Tile 12" x 12", Ramps 6" x 12", Corners 6" x 6"
- Stock Sizes: 30" x 36", 30" x 48", 30" x 60", 30" x 72", 30" x 96", 42" x 72", 42" x 96", 42" x 120"



Anti-Slip