



CUSHION TRAX® (Best)
CUSHION TRAX® ULTRA™ (Superior)
SADDLE TRAX™ (Superior)

#479
 #975
 #979

The Cushion Trax® Series is engineered to meet the toughest requirements of today's industrial applications and allows you to select your level of comfort from three different thicknesses (9/16", 3/4", 1"). The durable vinyl diamond-plate design provides non-directional traction, and is easy to clean. The top surface is combined with a dense closed cell foam base utilizing NoTrax® exclusive UniFusion™ technology virtually eliminating the possibility of de-lamination.

Where to use:

Machine operating stations or multi-shift dry applications needing fatigue prevention and sure footing.

Product info:

- Durable vinyl diamond-plate top surface is combined with dense closed cell foam base utilizing NOTRAX® exclusive UniFusion™ technology
- UniFusion™ bond guaranteed for the life of the mat – See warranty for details
- Top surface made from 100% recycled PVC
- RedStop™ non-slip backing technology
- Sloped beveled foam on all 4 undersides affords easy access onto and off of mat
- Certified by the NFSI (National Floor Safety Institute)
- Overall Thickness: 9/16" (#479), 3/4" (#975), 1" (#979)

Stock Sizes: 2' x 3', 3' x 5', 3' x 12'
Roll Sizes: 2' x 75', 3' x 75', 4' x 75'
Custom Sizes: In 2', 3', 4', and 5' widths (up to 75')



WEAR RESISTANCE	ANTI-FATIGUE PERFORMANCE	SLIP RESISTANCE
SUPERIOR	SUPERIOR	SUPERIOR
975 979	975 979	975 979
BEST	BEST	BEST
479	479	479

Safety/Anti-Fatigue – Laminates - "Diamond Plate"

