

### ABOUT JOHNSON DOT LASERS:

Johnson Level's Dot Laser line is the best choice to find a level point, or points, at 90° between a wall, the floor and the ceiling. All Johnson dot lasers are self-leveling, so an accurate measurement is obtained instantly, even on uneven ground. Johnson dot lasers are easy to see because of the concentrated beam for all indoor construction applications and are available in two-beam, three-beam, and five-beam dot laser models to meet the needs of every construction application.

### DOT LASER APPLICATIONS:

Setting foundations and footings, alignment of concrete forms, layout of interior walls, room additions/partition installation, install sprinkler systems, HVAC, plumbing and pipe installation, machinery installation, electrical outlets and switches, install conduit & wiring, track and canned lighting, align brick, square up better boards, align fences, plumb posts & pickets, align 90° joints and edges, level cabinets, shelving & countertops.



### SELF-LEVELING 5 BEAM DOT LASER

#### FEATURES:

- Self-leveling
- Projects five self-leveling beams simultaneously
- Locking mechanism protects inner pendulum during transportation
- Visual and audible alarms when beyond leveling range
- Laser can be rotated 360° when attached to magnetic laser mount



**1YRVZ INCLUDES:** Laser, multi-functional magnetic base, 3 "AA" alkaline batteries, mounting strap, magnetic target, tinted glasses, instruction manual with warranty card, soft-sided carrying case



#### FEATURES:

- Precision crafted anodized, machined aluminum frame for superior accuracy and durability
- Four vials read plumb, level, 45°, and cross check
- Three 90° beams emit simultaneous level, plumb and square reference points
- Strong magnetic base, tripod mount and v-groove frame for maximum versatility
- Leveling base included

**1YRT1 INCLUDES:** Laser, leveling base, 3 "AA" alkaline batteries, instruction manual with warranty card, soft-sided carrying pouch



For Product Information & Videos,  
Visit [GRAINGER.LASERS101.COM](http://GRAINGER.LASERS101.COM).



AVAILABLE THROUGH

# GRAINGER<sup>®</sup>

FOR THE ONES WHO GET IT DONE



**FEATURES:**

- Locking mechanism protects inner pendulum during transportation
- Projects three self-leveling beams (2CGJ6) or two self-leveling beams (4WMA6) simultaneously
- Visual and audible alarms when beyond leveling range



MAGNETIC TORPEDO LASER LEVEL



**FEATURES:**

- Aluminum frame for superior accuracy and durability
- Four vials read plumb, level, 45°, and cross check
- Built-in, rotating head swivels to project laser dot, horizontal or vertical line



**TYRR9 INCLUDES:** Laser, 2 “AAA” alkaline batteries, instruction manual with warranty card, soft-sided pouch

ELECTRONIC SELF-LEVELING PIPE LASER



**FEATURES:**

- Large, illuminated LCD display makes information easy to see and use
- Easy grade input to enter by individual digit for quick set-up changes
- Infrared remote control works over long distances providing real time data between remote and pipe laser
- Laser dot center feature automatically centers laser dot on target
- Battery indicator monitors battery level in rechargeable and alkaline battery packs
- Sleep mode turns off laser beam and display

**APPLICATIONS:**

Aligning storm, sanitary or other gravity flow drainage pipe

**5TCX2 KIT INCLUDES:** Laser, NiMH rechargeable battery pack, alkaline battery compartment, remote control with 9V battery, small and large target, car adapter charger with conversion plug, 6.4V AC battery adapter, 5 leg sets, instruction manual with warranty card, hard-shell carrying case

For Product Information & Videos,  
Visit [GRAINGER.LASERS101.COM](http://GRAINGER.LASERS101.COM).



AVAILABLE THROUGH

**GRAINGER**

FOR THE ONES WHO GET IT DONE