

An easy and flexible way to do gas detection.

IBRID™ MX6



Get ready to see hazardous levels of oxygen, toxic and combustible gas, and volatile organic compounds (VOCs) like never before.

The MX6 iBrid™ is more than an intelligent hybrid of Industrial Scientific's best monitoring technologies. It's the first gas monitor to feature a full-color LCD display screen.

The display improves safety with clear readings in low-light, bright-light or anywhere in between. Whether the work is outside, inside or underground, it's easy to see what gas hazards lurk in the immediate work environment.

And a color display is more than eye-catching. It allows the user to step through instrument settings and functions with an intuitive menu and the instrument's five-way navigation button. It even supports the option of on-board graphing for easily interpreted direct readings and recorded data.

Plus, the MX6 iBrid is our most rugged instrument ever. It is compatible with our DSX™ Docking Station and iNet.

The Gas Detection People

**INDUSTRIAL
SCIENTIFIC**

www.indsci.com



Don't Buy Gas Detectors

Subscribe to Gas Detection as a Service

It gives you help from The Gas Detection People.

Let us handle your gas detection program. Gas detection is probably not core to what you do. But, it's all that we do. It's what we love to do.

It gives you a safer workplace.

On average, gas detectors go into high alarm once every ten days. How many high alarms did your facility have? iNet gives you information and tools to fix problems before they happen.

It gives you cost savings.

The list price is only part of a gas detector's total cost. You have to maintain it. You have to wait for it to be serviced. iNet eliminates unnecessary ownership and maintenance costs.

iNet Compatible for Increased Safety, Cost Savings and Productivity

iNet is a software-based service that manages your fleet of gas detectors. iNet solves the most common gas detection problems. For example, iNet keeps people safe by providing visibility into alarms, exposure and usage. It keeps gas detectors working without costly and time-consuming maintenance. And with iNet, you won't have to buy the MX6. So why do it?

How Does iNet Work?



1. Operators dock gas detectors owned by Industrial Scientific.



2. Docking Stations perform bump tests, calibrations and record-keeping.

iNet



3. iNet Control provides visibility into your gas detection program via the Web.



4. iNet e-mails real-time alerts and status reports.




5. When iNet detects a problem, Industrial Scientific rushes a replacement gas detector to you.




THE MX6 iBRID COLOR DISPLAY


Enhanced Visibility – Expanded Functionality




The MX6 clearly shows real-time readings in PPM or % by volume.




An intuitive menu provides easy access to features and setup.




Datalog trends and direct readings can be viewed graphically.




Calibration progress and results are shown for each sensor.




A “calibration due” warning appears for each relevant sensor.



Bright red numerals and a flashing backlight show alarm conditions.



Alarms shown with “Go/No Go” text and flashing backlight.



Color-coded text shows test or calibration results at a glance.

INDUSTRIAL SCIENTIFIC

www.indsci.com

| MX6 BASE UNIT | SENSORS OPTIONS | BATTERY OPTIONS | VERSION OPTIONS | AGENCY CERTIFICATIONS | LANGUAGE OPTIONS | |
|---|---|-------------------|-----------------|-----------------------|------------------|------------|
| Supplied with monitor: Universal charger, nylon carrying case, belt clip, calibration cup, wrist strap, manual, quick start guide, dust filter/water stop (with pump), sample tubing (with pump). | Combustible Gases: LEL (Pentane) LEL (Methane) CH ₄ IR (0-100% vol.) CH ₄ (0-5%) Hydrocarbons IR (0-100% LEL) Volatile Organic Compounds: PID Toxic Gases: H ₂ S O ₂ NO ₂ CO CO/H ₂ S NH ₃ Cl ₂ ClO ₂ PH ₃ CO High SO ₂ HCl HCN H ₂ PH ₃ High NO CO/H ₂ low interference CO ₂ IR | Li-ion | Diffusion | UL/CSA | English | Portuguese |
| | | Li-ion/Ext. Range | Pump | ATEX/IECEX | French | Indonesian |
| | | Alkaline | | MSHA/ANZEx | Spanish | Russian |
| | | | | GOST-R | German | Polish |
| | | | | INMETRO | Italian | Czech |
| | | | | KOSHA | Dutch | |
| | | | | China EX | | |
| | | | | China CPC | | |
| | | | | | | |
| | | | | | | |

 **Build and price your MX6 online with the MX6 instrument builder.**
www.indsci.com/MX6builder.asp

| COMMON INSTRUMENT CONFIGURATIONS | |
|----------------------------------|--|
| PART NO. | DESCRIPTION |
| MX6-K1230201 | MX6 - LEL (Pentane), CO, H ₂ S, O ₂ , Ext. Li-ion |
| MX6-K123R111 | MX6 - LEL (Pentane), CO, H ₂ S, O ₂ , PID, Li-ion, Pump |
| MX6-L1230111 | MX6 - LEL (Methane), CO, H ₂ S, O ₂ , Li-ion, Pump |
| MX6-M103Q211 | MX6 - Methane, CO, O ₂ , CO ₂ IR, Ext. Li-ion, Pump |
| MX6-MDH34211 | MX6 - Methane, NO, CO high range, O ₂ , NO ₂ , Ext. Li-ion, Pump |
| MX6-K1235111 | MX6 - LEL (Pentane), CO, H ₂ S, O ₂ , SO ₂ , Li-ion, Pump |
| MX6-KJ635101 | MX6 - LEL (Pentane), CO/H ₂ S, NH ₃ , O ₂ , SO ₂ , Li-ion |
| MX6-MH23Q201 | MX6 - Methane, CO high range, H ₂ S, O ₂ , CO ₂ , Ext Li-ion |
| COMMON INDUSTRY CONFIGURATIONS | |
| MX6-KJ53R211 | MX6 - LEL, CO/H ₂ S, O ₂ , SO ₂ , PID, Extended Li-ion, Pump Petroleum Refining |
| MX6-K103Q211 | MX6 - LEL, CO, O ₂ , CO ₂ , Extended Li-ion, Pump Brewing/Bottling/Wineries |
| MX6-KJ835101 | MX6 - LEL, CO/H ₂ S, O ₂ , SO ₂ , ClO ₂ , Li-ion Pulp/Paper |
| MX6-K673R211 | MX6 - LEL, O ₂ , NH ₃ , Cl ₂ , PID, Extended Li-ion, Pump HazMat |
| MX6-M1030401 | MX6 - CH ₄ (%), CO, O ₂ , Li-ion (MSHA/AUS) Mining |
| MX6-M1D34401 | MX6 - CH ₄ (%), CO, O ₂ , NO ₂ , NO, Li-ion Extended (MSHA/AUS) Mining (Diesel Applications) |

| ACCESSORIES | |
|------------------|--|
| PART NO. | DESCRIPTION |
| MX6KIT-0000R211 | MX6 kit - PID, Extended Li-ion, with pump |
| MX6KIT-K1230211 | Confined space kit, 4-gas with pump |
| MX6KIT-K123R211 | Confined space kit, 4-gas/PID with pump |
| 18109329-ABC-ABC | DSX™ Docking Station for MX6 A – DSX Mode: 0 = DSX Standalone 1 = DSXi Cloud-connected 2 = DSX-L Local Server B – Number of Gas Inlet Ports: 3 = 3 Ports 6 = 6 Ports C – Power Cord Type: 0 = None, 1 = North America, 2 = EU, 3 = AUS, 4 = UK |
| 18106765 | SP6 motorized sampling pump module |
| 18107086 | MX6 datalink assembly – software included |
| 18106971 | MX6 replacement battery charger |
| 18107094 | MX6 battery charger/datalink, universal |
| 18107011 | MX6 battery charger, 12V |
| 18107136 | MX6 battery charger, 5-Unit |
| 18107243 | MX6 truck-mount charger, 12V |
| 18107250 | MX6 truck-mount charger, (hard-wired) |
| 17131038-1 | Rechargeable Li-ion battery pack, UL/CSA/ATEX/IECEX/GOST-R/KOSHA |
| 17131038-2 | Rechargeable Li-ion extended battery pack, UL/CSA/ATEX/IECEX/GOST-R/KOSHA |
| 17131038-4 | Rechargeable Li-ion battery pack, MSHA/AUS |
| 17131038-5 | Rechargeable Li-ion extended battery pack, MSHA/AUS |
| 17131046-3 | Alkaline battery pack, UL/CSA/ATEX/IECEX/GOST-R/KOSHA |
| 17131046-6 | Alkaline battery pack, MSHA/AUS |
| 18106856-0 | MX6 without pump, hard leather carrying case |
| 18106856-1 | MX6 without pump, hard leather case, no display window |
| 18106880-0 | MX6 with pump, hard leather carrying case |
| 18106880-1 | MX6 with pump, hard leather case, no display window |
| 18106831 | Nylon carrying case, supplied with MX6 without pump |
| 18106864 | Nylon carrying case, supplied with MX6/SP6 with pump |
| 17095746 | MX6/iTX maintenance tool |
| 17128489 | MX6 Calibration cup |
| 17153749 | MX6 screen protector, 10 pack |
| 17153760 | MX6 screen protector, 100 pack |



The DSX™ Docking Station easily maintains the gas detectors that keep your people safe in hazardous environments.

- Know that your gas detectors are ready for use every day, every shift, without the burden of manual maintenance routines.
- Stop worrying about calibration gas and let the DSX monitor and order replacement gas cylinders when you need them.
- Effortlessly manage your fleet, data, and software updates from any web-enabled device.

SP6 MOTORIZED SAMPLING PUMP



CHARGER / DATALINK

- Instantly download event logs and datalog data while instrument battery charges
- Quickly and easily configure instrument settings



MULTI-UNIT CHARGER

CHARGER



LEATHER CASES



TRUCK MOUNT CHARGER

MX6 CONFINED SPACE KIT

Cylinder shown with iGas Card Reader



Choice of MX6 monitor, universal charger, nylon carrying case, belt clip, calibration cup, wrist strap, maintenance tool, manual, quick start guide, calibration tubing, dust filter/water stop (with pump), calibration fitting (with pump), sample tubing (with pump), calibration gas (appropriate mix) with regulator, spare replaceable cell alkaline battery pack, rugged Pelican® case.

INSTRUMENT WARRANTY:

Warranted for as long as the instrument is supported by Industrial Scientific Corporation

CASE MATERIAL:

Lexan/ABS/Stainless Steel w/protective rubber overmold

DIMENSIONS:

135 mm x 77 mm x 43 mm (5.3" x 3.05" x 1.7") – without pump
167 mm x 77 mm x 56 mm (6.6" x 3.1" x 2.2") – with pump

WEIGHT:

409 g (14.4 oz) typical – without pump
511 g (18.0 oz) typical – with pump

DISPLAY/READOUT:

Color Graphic Liquid Crystal Display

POWER SOURCE/RUN TIMES:

Rechargeable Lithium-ion (Li-ion) Battery Pack (24 hours) – without pump
Rechargeable, Extended-Range Lithium-ion (Li-ion) Battery Pack (36 hours) – without pump
Replaceable AA Alkaline Battery Pack (10.5 hours) – without pump

OPERATING TEMPERATURE RANGE:

-20°C to 55°C (-4°F to 131°F)

OPERATING HUMIDITY RANGE:

15% to 95% non-condensing (continuous)

MEASURING RANGES:

| SENSOR | RANGE | RESOLUTION |
|---|--|------------|
| CATALYTIC BEAD | | |
| Combustible Gas | 0-100% LEL | 1% |
| Methane | 0-5% vol | 0.01% |
| ELECTROCHEMICAL | | |
| Ammonia | 0-500 ppm | 1 |
| Carbon Monoxide | 0-1,500 ppm | 1 |
| Carbon Monoxide (High Range) | 0-9,999 ppm | 1 |
| Carbon Monoxide/Hydrogen low | 0-1,000 ppm | 1 |
| Chlorine | 0-50 ppm | 0.1 |
| Chlorine Dioxide | 0-1 ppm | 0.01 |
| Carbon Monoxide/ Hydrogen Sulfide (COSH) | CO: 0-1,500 ppm H ₂ S: 0-500 ppm | 1 0.1 |
| Hydrogen | 0-2,000 ppm | 1 |
| Hydrogen Chloride | 0-30 ppm | 0.1 |
| Hydrogen Cyanide | 0-30 ppm | 0.1 |
| Hydrogen Sulfide | 0-500 ppm | 0.1 |
| Nitric Oxide | 0-1,000 ppm | 1 |
| Nitrogen Dioxide | 0-150 ppm | 0.1 |
| Oxygen | 0-30% vol | 0.1% |
| Phosphine | 0-5 ppm | 0.01 |
| Phosphine (High Range) | 0-1,000 ppm | 1 |
| Sulfur Dioxide | 0-150 ppm | 0.1 |
| INFRARED | | |
| Hydrocarbons | 0-100% LEL | 1% |
| Methane (% vol) | 0-100% vol | 1% |
| Methane (% LEL) | 0-100% LEL | 1% |
| Carbon Dioxide | 0-5% vol | 0.01% |
| PHOTOIONIZATION | | |
| VOC | 0-2,000 ppm | 0.1 |

CERTIFICATIONS:

UL: Class I, Groups A,B,C,D T4; Class II, Groups F,G; AEx ia d IIC T4
CSA: Class I, Groups A,B,C,D T4; Ex d ia IIC T4
MSHA: CFR30, Part 22, Intrinsically safe for methane/air mixtures
ATEX: Ex ia IIC T4 Ga / Ex ia I Ma; IP64;
Equipment Group and Category: II 1G / I M1 (I M2 w/IR sensor)
IECEX: Ex ia IIC T4 Ga / Ex ia I (Ex ia d I w/IR sensor)
ANZEx: Ex ia s Zone 0 I; IP64; Ex ia s Zone 0 IIC T4
INMETRO: Ex ia IIC T4 Ga
GOST-R: PBExiadl X / 1ExiadIIC T4 X
KOSHA: Ex d ia IIC T4
China Ex: Ex ia d IIC T4
China CPC: Metrology Approval

* These specifications are based on performance averages and may vary by instrument