

Water-Cooled TIG Torch Adapters



50 mm Dinse-Style with Water Return Line 195377

For Dynasty 210/300/400, Maxstar 210/280/400 and Syncrowave 300/400. Used with all Weldcraft™ water-cooled torches.



With gas and water return line.

50 mm Dinse-Style Flow Thru 195380

For Syncrowave 210. Used with all Weldcraft™ water-cooled torches.



50 mm Thread-Lock-Style 225028

For Dynasty 800 and Maxstar 800. Used with all Weldcraft™ water-cooled torches.



Water-Cooled TIG Block Adapter 45V11
For Miller power sources with stud-type output terminals.



Replacement Water Hose for Dinse-Style Adapter 222809 18 in. (457 mm)

Water Hoses and Connectors



Water Hose Extension 40V76R6

6 ft. (1.8 m). Hose with two male 5/8-inch 18 LH thread connections.



Water Coupler 057020

Brass hose fitting with 5/8-inch 18 LH thread.

Coolants



Must be ordered in quantities of four. One-gallon recyclable plastic bottle. Miller coolants contain a base of ethylene glycol and deionized water to protect against freezing to -37° Fahrenheit (-38° C) or boiling to 227° Fahrenheit (108° C).

Low-Conductivity Coolant (clear, pre-mixed) 043810

For TIG and MIG applications. NOT for use in push-pull systems or systems where aluminum is in coolant path/circuit.

Aluminum-Protecting Coolant (green, pre-mixed) 043809

Primarily used in push-pull systems where aluminum is in coolant path/circuit and high frequency is NOT used.

Replacement Filter Assemblies



166564 filter



215667 filter

Filter Assemblies

166564 For Coolmate 1.3, 3 and 3X

215667 For Coolmate 3.5



Filter Strainer 146249

For Coolmate 4. Located inside pump assembly. See owner's manual.

Torch Kits



W-250 (WP-20) Torch Kit 300185

- Weldcraft™ W-250 25-foot (7.6 m) TIG torch with Dinse-style connector
- Torch cable cover
- Work clamp with 15-foot (4.6 m) 1/0 cable and Dinse-style connector
- Flowmeter regulator
- Gas hose (regulator to machine)
- AK4GL torch accessory kit includes short back cap, nozzles, gas lenses, collets and 2% ceriated tungsten electrodes (1/16, 3/32 and 1/8 inch)



W-375 Torch Kit 301268

- Weldcraft™ W-375 25-foot (7.6 m) TIG torch with Dinse-style connector
- Torch cable cover
- Work clamp with 15-foot (4.6 m) 1/0 cable and Dinse-style connector
- Flowmeter regulator
- Gas hose (regulator to machine)
- AK4GL torch accessory kit includes short back cap, nozzles, gas lenses, collets and 2% ceriated tungsten electrodes (1/16, 3/32 and 1/8 inch)



W-280 (WP-280) Torch Kit 300990

- Weldcraft™ W-280 25-foot (7.6 m) TIG torch with Dinse-style connector
- Torch cable cover
- Work clamp with 15-foot (4.6 m) 1/0 cable and Dinse-style connector
- Flowmeter regulator
- Gas hose (regulator to machine)
- AK4GL torch accessory kit includes short back cap, nozzles, gas lenses, collets and 2% ceriated tungsten electrodes (1/16, 3/32 and 1/8 inch)



W-400 (WP-18SC) Torch Kit 300186

- Weldcraft™ W-400 25-foot (7.6 m) TIG torch with thread-lock connector
- Torch cable cover
- Work clamp with 12-foot (3.7 m) 4/0 cable with thread-lock connector
- Flowmeter regulator
- Gas hose (regulator to machine)
- AK18C torch accessory kit includes short back cap, nozzles, collets, collet bodies and 2% ceriated tungsten electrodes (3/32, 1/8 and 5/32 inch)