


Miller Titan T8221 Rebar Positioning Assembly

Description
 The **T8221** is a Rebar Positioning Assembly with a 13-link chain, two locking snap hooks and one locking rebar hook. This product is to be used for positioning only.



Materials

Hardware: Steel Minimum Tensile strength
 Locking Snap Hooks 5000 lbs. (22kN), 3/4" (19mm) gate opening
 Locking Rebar Hooks 5,000 lbs. (22kN), 2 1/2" (63mm) gate opening
 * All hardware meets ASTM (50) fifty-hour salt spray test requirements.

Technical

Max Working Load: 310 lbs -140.62 kg

Identification

Label Materials: Lexan and Valeron

Certifications

Meets OSHA 1926.502 and ANSI A10.14 type II requirements.



by Honeywell

Toll Free 800.873.5242 (press 4) • hsptechsupport@honeywell.com • www.millerfallprotection.com

WARNING! THIS DOCUMENT PROVIDES AN OVERVIEW OF FALL PROTECTION PRODUCTS AVAILABLE FROM HONEYWELL AND CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE DATA. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. HONEYWELL RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THE PRODUCTS BE THOROUGHLY READ AND UNDERSTOOD PRIOR TO EACH USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.