



Available Colors: Burgundy, Brown, Slate Blue, Gray, Hunter Green, Charcoal, & Red/Black.



**B**arrier Rib® is a unique yet highly functional indoor entrance mat with a molded dual-ridge cross-rib pattern to maximize the scraping and drying process. A raised rubber perimeter on all four sides of the mat retains moisture and debris, and an anti-microbial carpet treatment stops bacteria and germs at the entrance. An extremely durable rubber backed mat, Barrier Rib® has a highly fashionable look that features carpet-to-the-edge choices to match any décor.

Test	Test Description	*Results
ASTM D3884-01	Abrasion Resistance	0.44 grams (1.1%)
ASTM D-5252-98	Accelerated Wear - 12,000 cycles (Hexapod Tumble Drum Tester)	Appearance: 3.0 Color: 3.5
ASTM D6540-00	Accelerated Soiling	Based on Visual Inspection 4.0 - Vacuum Rating 4.5 - Rating After Extraction
CPSC FF 1-70 ASTM D-2859	Surface Flammability of Carpets and Rugs Ignition Characteristics - Finished Textile Floor Covering Material	Pass
-	Water Retention	Weight Gain = 25.4% (0.279 gals./yd <sup>2</sup> )
AATCC Test Method 147	Antibacterial Activity	No Growth After 24 Hrs.
ASTM G22	Bacterial Resistance	No Growth After 21 Days
ASTM G21	Fungal Resistance	No Growth After 28 Days


\*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

07/2014

**Appearance Rating Key**

5	No change
4	Slight change
3	Noticeable change
2	Considerable change
1	Severe change

- Antimicrobial carpet treatment
- 26 oz. face weight
- Thickness: 3/8"
- Rubber underside cleat design resists mat slippage
- Stock Sizes: 2' x 3', 3' x 4', 3' x 5', 3' x 10', 4' x 6', 4' x 10'
- Custom Sizes: In 3' , and 4' widths (up to 60')
- Recommended and approved product as part of the GreenTRAX™ program for "Green Cleaning" environments



Custom Sizes