



1650 Large Case



- Retractable extension handle
- **4 strong polyurethane wheels with stainless steel bearings**
- Easy open Double Throw latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Fold down handles
- Stainless steel hardware and padlock protectors
- 2 level Pick N Pluck™ with convoluted lid foam
- [Personalized nameplate service available](#)
- **Watertight, crushproof, and dustproof**

CONFIGURATIONS

- 1650** - Standard
- 1654** - With With Padded Dividers
- 1650NF** - With No Foam
- 1650TP** - With With TrekPak Divider System

DIMENSIONS

- Interior (L x W x D):** 28.57 x 17.52" x 10.65 (72.6 x 44.5 x 27.1 cm)
- Exterior (L x W x D):** 31.59 x 20.47" x 12.45 (80.2 x 52 x 31.6 cm)
- Lid Depth:** 1.81" (4.6 cm)
- Bottom Depth:** 8.84" (22.5 cm)
- Total Depth:** 10.65" (27.1 cm)
- Int Volume:** 3.08 ft³ (0.087 m³)


MATERIALS

- Body:** Polypropylene
- Latch:** ABS
- O-Ring:** Polymer
- Pins:** Stainless Steel
- Foam:** 1.3 lb Polyurethane
- Purge Body:** ABS
- Purge Vent:** 3 Micron Hydrophobic Non-Woven
- Purge O-Ring:** 70 Shore Nitrile

COLORS

 Black

 OD Green

 Desert Tan

WEIGHT

Weight With Foam: 28.06 lbs (12.7 kg)

Weight Without Foam: 24.03 lbs (10.9 kg)

Buoyancy: 181.00 lbs (82.1 kg)

Master Pack Weight: 30.10 lbs (13.7 kg)

TEMPERATURE

Minimum Temperature: -40°

Maximum Temperature: 210°

CERTIFICATIONS

IP67

MIL C-4150J

Def Stan 81-41

STANAG 4280

ATA 300

FOAM PROPERTIES

Layer 1 (Lid): 1.75" Convolute

Layer 2 (Base): 1.00" Pad

Layer 3 (Base): 3.75" Pick N Pluck

Layer 4 (Base): 3.75" Pick N Pluck

OTHER

Wheels: 4

Extendable Handle: yes

Master Pack: 1

Nameplate: yes

Reduced Area: yes

Military: yes

Pelican Products, Inc.

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311

sales@pelican.com • www.pelican.com