



Rating		Pin and Sleeve Devices							Accessories	
Amps	Poles and Wires	Configuration Recept./ Plug/ Conn. Inlet	AC Voltage	Connector	Receptacle	HP	Mating Plug**	IP67 Inlet	Back Boxes	Closure Caps
30	2P 3W		125V	HBLS330C4W	HBLS330R4W	2	HBLS330P4W	HBL330B4W	BB2030N	PC3430
32	2P 3W		100-130V	HBLS332C4W	HBLS332R4W	2	HBLS332P4W	HBL332B4W	BB2030N	PC3430
30	2P 3W		250V	HBLS330C6W*	HBLS330R6W*	5	HBLS330P6W*	HBL330B6W*	BB2030N	PC3430
32	2P 3W		220-240V							
30	2P 3W		480V	HBLS330C7W	HBLS330R7W	10	HBLS330P7W	HBL330B7W	BB2030N	PC3430
30	3P 4W		125/250V	HBLS430C12W	HBLS430R12W	2	HBLS430P12W	HBL430B12W	BB2030N	PC3430
30/32	3P 4W		3Ø 250V	HBLS430C9W*	HBLS430R9W*	10	HBLS430P9W*	HBL430B9W*	BB2030N	PC3430
30	3P 4W		3Ø 480V	HBLS430C7W	HBLS430R7W	20	HBLS430P7W	HBL430B7W	BB2030N	PC3430
30	3P 4W		3Ø 600V	HBLS430C5W	HBLS430R5W	30	HBLS430P5W	HBL430B5W	BB2030N	PC3430
30/32	3P 4W		380-415V	HBLS430C6W*	HBLS430R6W*	7.5	HBLS430P6W*	HBL430B6W*	BB2030N	PC3430
32	3P 4W		380-440V	HBLS432C3W	HBLS432R3W	10	HBLS432P3W	HBL432B3W	BB2030N	PC3430
30	4P 5W		3ØY 347/600V	HBLS530C5W	HBLS530R5W	30	HBLS530P5W	HBL530B5W	BB2030N	PC530
30	4P 5W		200/346- 240/415V	HBLS530C6W*	HBLS530R6W*	7.5	HBLS530P6W*	HBL530B6W*	BB2030N	PC530
32	4P 5W		220/380V 240/415V							
30	4P 5W		3ØY 277/480V	HBLS530C7W	HBLS530R7W	20	HBLS530P7W	HBL530B7W	BB2030N	PC530
30/32	4P 5W		3ØY 120/208V	HBLS530C9W*	HBLS530R9W*	10	HBLS530P9W*	HBL530B9W*	BB2030N	PC530
60	2P 3W		125V	HBLS360C4W	HBLS360R4W	3	HBLS360P4W	HBLS360B4W	BB60N	PC60
60	2P 3W		250V	HBLS360C6W*	HBLS360R6W*	7.5	HBLS360P6W*	HBL360B6W*	BB60N	PC60
63	2P 3W		220-240V							
60	2P 3W		480V	HBLS360C7W	HBLS360R7W	15	HBLS360P7W	HBL360B7W	BB60N	PC60
60	3P 4W		125/250V	HBLS460C12W	HBLS460R12W	3	HBLS460P12W	HBL460B12W	BB60N	PC60
60/63	3P 4W		3Ø 250V	HBLS460C9W*	HBLS460R9W*	10	HBLS460P9W*	HBL460B9W*	BB60N	PC60
60	3P 4W		3Ø 480V	HBLS460C7W	HBLS460R7W	30	HBLS460P7W	HBL460B7W	BB60N	PC60
60	3P 4W		3Ø 600V	HBLS460C5W	HBLS460R5W	40	HBLS460P5W	HBL460B5W	BB60N	PC60
60/63	3P 4W		380-415V	HBLS460C6W*	HBLS460R6W*	10	HBLS460P6W*	HBL460B6W*	BB60N	PC60
60	4P 5W		3ØY 347/600V	HBLS560C5W	HBLS560R5W	40	HBLS560P5W	HBL560B5W	BB60N	PC60
60/63	4P 5W		200/346- 240/415V	HBLS560C6W*	HBLS560R6W*	10	HBLS560P6W*	HBL560B6W*	BB60N	PC60
60	4P 5W		3ØY 277/480V	HBLS560C7W	HBLS560R7W	30	HBLS560P7W	HBL560B7W	BB60N	PC60
60/63	4P 5W		3ØY 120/208V	HBLS560C9W*	HBLS560R9W*	10	HBLS560P9W*	HBL560B9W*	BB60N	PC60

Note: \*Certain IEC configurations allow for a single product to be certified as both a North American (Series 2) and International amperage (Series 1). These products are marked accordingly with both the UL Listing and UL Classified markings.

\*\*Mating plug or inlet required to maintain 4X/IP69k ratings when used with ADVANTAGE™ series connections.  
 ADVANTAGE™ series receptacles have the same mounting pattern as standard Hubbell IEC pin and sleeve.  
 Just add a "P" suffix for Pilot pin for 60 amp devices.