



1660 Large Case



- Retractable extension handle
- **4 strong polyurethane wheels with stainless steel bearings**
- Easy open Double Throw latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- **Large 2-person fold down handles**
- Stainless steel hardware and padlock protectors
- 3 level Pick N Pluck™ with convoluted lid foam
- [Personalized nameplate service available](#)
- **Watertight, crushproof, and dustproof**

CONFIGURATIONS

- 1660** - Standard
- 1664** - With With Padded Dividers
- 1660NF** - With No Foam

DIMENSIONS

- Interior (L x W x D):** 28.20 x 19.66" x 17.63 (71.6 x 49.9 x 44.8 cm)
- Exterior (L x W x D):** 31.59 x 22.99" x 19.48 (80.2 x 58.4 x 49.5 cm)
- Lid Depth:** 3.50" (8.9 cm)
- Bottom Depth:** 14.14" (35.9 cm)
- Total Depth:** 17.64" (44.8 cm)
- Int Volume:** 5.66 ft³ (0.16 m³)

MATERIALS

- Body:** Polypropylene
- Latch:** ABS
- O-Ring:** Polymer
- Pins:** Stainless Steel
- Foam:** 1.3 lb Polyurethane
- Purge Body:** ABS
- Purge Vent:** 3 Micron Hydrophobic Non-Woven
- Purge O-Ring:** 70 Shore Nitrile

COLORS



Black



OD Green



Desert Tan

WEIGHT

Weight With Foam: 42.16 lbs (19.1 kg)

Weight Without Foam: 34.16 lbs (15.5 kg)

Buoyancy: 365.00 lbs (165.6 kg)

Master Pack Weight: 49.00 lbs (22.2 kg)

TEMPERATURE

Minimum Temperature: -40°

Maximum Temperature: 210°

CERTIFICATIONS

IP67

Def Stan 81-41

STANAG 4280

FOAM PROPERTIES

Layer 1 (Lid): 3.00" Convolute

Layer 2 (Base): 1.00" Pad

Layer 3 (Base): 4.25" Pick N Pluck

Layer 4 (Base): 4.25" Pick N Pluck

Layer 5 (Base): 4.25" Pick N Pluck

OTHER

Wheels: 4

Extendable Handle: yes

Master Pack: 1

Nameplate: yes

Reduced Area: yes

Military: yes

Pelican Products, Inc.

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311

sales@pelican.com • www.pelican.com