


1890 Swarthmore Avenue, PO Box 2020, Lakewood, NJ 08701 Phone: 800-526-3694, 732-363-4700, Fax: 732-364-8110 www.encoreplumbing.com • www.componenthardware.com

Encore [®] Wall Mount Faucet with
Tubular Swing Spout and Lever Handles

KL54-8xxx-SE1 Series

KL54-8106-SE1	6" Spout, Ceramic Valves
KL54-8006-SE1 KL54-8108-SE1	6" Spout, Compression Valves 8" Spout, Ceramic Valves
KL54-8008-SE1	8" Spout, Compression Valves
KL54-8110-SE1	10" Spout, Ceramic Valves
KL54-8010-SE1	10" Spout, Compression Valves
KL54-8112-SE1	12" Spout, Ceramic Valves
KL54-8012-SE1	12" Spout, Compression Valves
KL54-8114-SE1	14" Spout, Ceramic Valves
KL54-8014-SE1	14" Spout, Compression Valves
KL54-8116-SE1	16" Spout, Ceramic Valves
KL54-8016-SE1	16" Spout, Compression Valves





Dimensions shown in inches (mm) are for reference only and are subject to change.

1-1/2" (29mm) hole for backsplash is recommended to accommodate 1/2" supply nipples. 1/2" NPT Female Inlets Operating Temperature: 40 - 180°F (5 - 83°C) Operating Pressure: 15 - 125psi

Approximate shipping weight - 5 lbs Warranty - 2 years parts

PROJECT NAME:	
LOCATION:	
SPECIFIER ITEM NO.	

QTY:

ENCORE PART NO.

Solid heavy duty cast body is specification and commercial quality

Commercial Quality Features

- Tubular swing spout design
- ADA-compliant lever handles
- · Built-in check valve to prevent cross-flow and back-flow
- Leak proof double O-ring spout design
- Stainless steel spout

SPECIFICATIONS:

Wall Mount Faucet to be Encore KL54 Series in the following configuration:

KL54-8106-SE1	6" Spout, Ceramic Valves
KL54-8006-SE1	6" Spout, Compression Valves
KL54-8108-SE1	8" Spout, Ceramic Valves
KL54-8008-SE1	8" Spout, Compression Valves
KL54-8110-SE1	10" Spout, Ceramic Valves
KL54-8010-SE1	10" Spout, Compression Valves
KL54-8112-SE1	12" Spout, Ceramic Valves
KL54-8012-SE1	12" Spout, Compression Valves
KL54-8114-SE1	14" Spout, Ceramic Valves
KL54-8014-SE1	14" Spout, Compression Valves
KL54-8116-SE1	16" Spout, Ceramic Valves
KL54-8016-SE1	16" Spout, Compression Valves

Faucet body to be constructed of polished chrome plated brass with total lead content less than 0.25% by weighted average. Valves to be 1/4-turn with integral check valve to prevent cross-flow and back-flow. Spout to be stainless steel tubular swing style with leak proof double O-ring seal design. Color coded temperature indexes shall meet international standards. 2.2gpm aerator @ 60psi standard with full flow stream bubbler screen spout tip.

Model No.	А	В	С
KL54-8106-SE1	6" (152mm)	5-9/16" (141mm)	3-5/16" (84mm)
KL54-8006-SE1	6" (152mm)	5-9/16" (141mm)	3-5/16" (84mm)
KL54-8108-SE1	8" (203mm)	6-1/16" (154mm)	3-13/16" (96mm)
KL54-8008-SE1	8" (203mm)	6-1/16" (154mm)	3-13/16" (96mm)
KL54-8110-SE1	10" (254mm)	6-1/2" (165mm)	4-1/4" (108mm)
KL54-8010-SE1	10" (254mm)	6-1/2" (165mm)	4-1/4" (108mm)
KL54-8112-SE1	12" (305mm)	6-15/16" (176mm)	4-11/16" (120mm)
KL54-8012-SE1	12" (305mm)	6-15/16" (176mm)	4-11/16" (120mm)
KL54-8114-SE1	14" (355mm)	7-7/16" (187mm)	5-3/16" (131mm)
KL54-8014-SE1	14" (355mm)	7-7/16" (187mm)	5-3/16" (131mm)
KL54-8116-SE1	16" (406mm)	7-7/8" (200mm)	5-5/8" (143mm)
KL54-8016-SE1	16" (406mm)	7-7/8" (200mm)	5-5/8" (143mm)

COMPLIES WITH: THE FEDERAL "REDUCTION OF LEAD IN DRINKING WATER ACT" – 2011 – US SENATE BILL NO. S.3874 NSF/ANSI 61/9, ANNEX G





Faucet Configurator for KL54-8000 Series



1890 Swarthmore Avenue, PO Box 2020, Lakewood, NJ 08701 Phone: 800-526-3694, 732-363-4700, Fax: 732-364-8110 www.encoreplumbing.com

BODY KL54 = CP POLISHED BRASS SPLASH MOUNT FAUCET BODY WITH ADJUSTABLE SPOUT OUTLET INLET 8 = 8" (203mm) CTR- 1/2" NPSM INTEGRAL CAST INLETS 1 = 8" (203mm) WITH 2-1/2" OFFSET SUPPLY INLETS WITH BUILT-IN STOPS VALVE 0 = 1/4 TURN STANDARD ENCORE® COMPRESSION VALVE W/BUILT IN CHECK 1 = 1/4 TURN CERAMIC VALVE W/ INLINE CHECK VALVE 2 = SELF CLOSING ADJUSTABLE METERING VALVE SPOUT 00 = 3-1/2" (89mm) GOOSENECK 01 = 8-1/2" (216mm) GOOSENECK 02 = 6" (152mm) GOOSENECK 06 = 6" (152mm) TUBULAR OR CAST SWING SPOUT 08 = 8" (203mm) TUBULAR SWING SPOUT 10 = 10" (254mm) TUBULAR SWING SPOUT 12 = 12" (305mm) TUBULAR SWING SPOUT 14 = 14" (356mm) TUBULAR SWING SPOUT 16 = 16" (406mm) TUBULAR SWING SPOUT 18A = 18" (457mm) TUBULAR SWING SPOUT 18 = 18" (457mm) DOUBLE JOINTED SWING SPOUT 24 = 24" (609mm) DOUBLE JOINTED SWING SPOUT SPOUT STYLE S = ADJUSTABLE SPOUT R = RIGID TUBULAR SPOUT T = CAST TUBULAR SPOUT (6" ONLY) AERATOR A = 0.5 GPM PCA SPRAY VANDAL RESISTANT B = 1.5 GPM MAX LAMINAR VANDAL RESISTANT C = 0.5 GPM PCA SPRAY D = 1.5 GPM MAX LAMINAR E = 2.2 GPM MAX AERATED STREAM F = 2.2 GPM MAX AERATED STREAM VANDAL RESISTANT G = .35 GPM PCA SPRAY (MALE) H = 2.2 GPM MAX AERATED STREAM VANDAL & HOSE RESISTANT J = .35 GPM PCA SPRAY K = .35 GPM PCA SPRAY (MALE) VANDAL RESISTANT L = .35 GPM PCA SPRAY VANDAL RESISTANT M = 1.0 GPM PCA LAMINAR FLOW S = 6.0 GPM MAX WIDE ROSE SPRAY HANDLE 1 = STANDARD ENCORE® LEVER 2 = CROSS 4 = 4" (102mm) WRIST BLADE

- 5 = STANDARD LEVER W/TAMPER PROOF SCREW
- 6 = 6" (152mm) WRIST BLADE SANIGUARD
- 7 = 4" (102mm) WRIST BLADE W/ TAMPER PROOF SCREW
- 8 = 6" (152mm) WRIST BLADE W/TAMPER PROOF SCREW