Product data sheet Characteristics

RXM4AB1B7

Harmony, Miniature plug-in relay, 6 A, 4 CO, with lockable test button, 24 V AC





Main

| Range of Product | Harmony Electromechanical Relays |
|--|----------------------------------|
| Series name | Miniature |
| Product or Component Type | Plug-in relay |
| Device short name | RXM |
| Contacts type and composition | 4 C/O |
| [Uc] control circuit voltage | 24 V AC 50/60 Hz |
| [Ithe] conventional enclosed thermal current | 6 A -40131 °F (-4055 °C) |
| Status LED | Without |
| Control Type | Lockable test button |
| Utilisation coefficient | 20 % |

Complementary

| Complementary | |
|--|-------------------------------------|
| Shape of pin | Flat |
| [Ui] rated insulation voltage | 250 V IEC |
| | 300 V CSA |
| | 300 V UL |
| [Uimp] rated impulse withstand voltage | 2.5 kV 1.2/50 μs |
| Contacts material | AgNi |
| [le] rated operational current | 3 A 28 V DC) NC IEC |
| | 3 A 250 V AC) NC IEC |
| | 6 A 28 V DC) NO IEC |
| | 6 A 250 V AC) NO IEC |
| | 6 A 277 V AC) UL 8 A 30 V DC) UL |
| | , |
| Maximum switching voltage | 250 V IEC |
| Resistive rated load | 6 A 250 V AC |
| | 6 A 28 V DC |
| Maximum switching capacity | 1500 VA/168 W |
| Minimum switching capacity | 170 mW 10 mA, 17 V |
| Operating rate | <= 1200 cycles/hour under load |
| | <= 18000 cycles/hour no-load |
| Mechanical durability | 10000000 cycles |
| Electrical durability | 100000 cycles resistive |
| Average coil consumption in VA | 1.2 60 Hz |
| Average consumption | 1.2 VA 60 Hz |
| Drop-out voltage threshold | >= 0.15 Uc |
| Operate time | 20 ms |
| Release time | 20 ms |
| Average coil resistance | 180 Ohm 20 °C +/- 15 % |
| Rated operational voltage limits | 19.226.4 V AC |
| Safety reliability data | B10d = 100000 |
| Protection category | RTI |
| Test levels | Level A |
| Operating position | Any position |
| CAD overall height | 3.11 in (79 mm) |

| CAD overall depth | 3.09 in (78.45 mm) |
|---------------------|------------------------|
| Net Weight | 0.08 lb(US) (0.037 kg) |
| Device presentation | Complete product |

Environment

| 2000 V AC between coil and contact | |
|---|---|
| 2000 V AC between poles | |
| CSA | |
| Lloyd's | |
| CE | |
| UL | |
| GOST | |
| CSA C22.2 No 14 | |
| UL 508 | |
| EN/IEC 61810-1 | |
| -40185 °F (-4085 °C) | |
| -40131 °F (-4055 °C) | |
| 3 gn +/- 1 mm 10150 Hz)5 cycles in operation | |
| 5 gn +/- 1 mm 10150 Hz)5 cycles not operating | |
| IP40 conforming to EN/IEC 60529 | |
| 10 gnin operation | |
| 30 gnnot operating | |
| 2 | |
| | 2000 V AC between poles CSA Lloyd's CE UL GOST CSA C22.2 No 14 UL 508 EN/IEC 61810-1 -40185 °F (-4085 °C) -40131 °F (-4055 °C) 3 gn +/- 1 mm 10150 Hz)5 cycles in operation 5 gn +/- 1 mm 10150 Hz)5 cycles not operating IP40 conforming to EN/IEC 60529 10 gnin operation 30 gnnot operating |

Ordering and shipping details

| 21127 - ZELIO ICE CUBE RELAYS |
|-------------------------------|
| CP2 |
| 3389119403702 |
| 1 |
| 1.41 oz (40 g) |
| Yes |
| CN |
| |

Packing Units

| Packing Units | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.61 in (4.1 cm) |
| Package 1 width | 1.10 in (2.8 cm) |
| Package 1 Length | 0.83 in (2.1 cm) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 13.90 oz (394 g) |
| Package 2 Height | 1.18 in (3 cm) |
| Package 2 width | 4.06 in (10.3 cm) |
| Package 2 Length | 4.92 in (12.5 cm) |
| Unit Type of Package 3 | S02 |
| Number of Units in Package 3 | 240 |
| Package 3 Weight | 21.94 lb(US) (9.95 kg) |
| Package 3 Height | 5.91 in (15 cm) |
| Package 3 width | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |
| | |

Offer Sustainability

Warranty


| Sustainable offer status | Green Premium product |
|----------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACh Regulation | REACh Declaration |
| REACh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EVEN RoHS |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | ₫Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

18 months


Product data sheet Dimensions Drawings

RXM4AB1B7


Dimensions




Pin Side View



Wiring Diagram






Symbols shown in blue correspond to Nema marking.

Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient.

Resistive AC load



X Switching capacity (kVA)

Y Durability (Number of operating cycles)


A RXM2AB•••

B RXM3AB•••

C RXM4AB•••


D RXM4GB•••

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

A RXM2AB•••

B RXM3AB•••

C RXM4AB•••

D RXM4GB•••

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.