

200 Series

PREMIUM ALL-STEEL



products meet or exceed applicable ANSI/BIFMA standards

MODEL 201 SHOWN



SPECS:

- Electromagnetically welded seat back
- Two U-shaped double riveted cross braces
- Features 18-gauge 7/8" round tubular frame
- Powder-coated frame
- Double hinges on each side for added stability and durability
- Color coordinated V-tip plugs for added stability
- Color coordinated polypropylene glides
- Features our unique full size double contoured square back and waterfall seat

DIMENSIONS:

OVERALL: 29 1/2"H x 18 1/4"W x 20 1/4"D


FOLDED: 38"H x 18 1/4"W x 2"D

SEAT: 17 1/4"H x 16"W x 16"D

BACK: 8 1/4"H x 18 1/4"W

480lb. weight capacity!

COLOR OPTIONS



USE WITH:

Model #84 Double-Tier Hanging Chair Truck

CAPACITY: HOLDS UP TO 84 FOLDING CHAIRS (200 SERIES)

Model #DY35/#DY50 Folding Chair Dolly

CAPACITY: DY35 HOLDS UP TO 35 FOLDING CHAIRS (200 SERIES) DY50 HOLDS UP TO 50 FOLDING CHAIRS (200 SERIES)

FOR VERTICAL FOLDING STORAGE



AVAILABLE ACCESSORIES



National Public Seating



800.261.4112 | www.nationalpublicseating.com

