



Cut



Medium Duty

High visibility glove keeps workers safe in low-light environments

- Visibility is a top priority on dangerous jobsites. It can help avoid injuries and save lives.
- ActivArmr 97-013 MD Hi-Viz™ gloves are specially designed with a highly reflective back to keep workers safe in low-visibility and dark environments.
- The gloves are engineered to the core with the industry leading combination of high-tech INTERCEPT™ technology hand protection plus all-day comfort and wet/dry grip that meets the demands of the job.



Industries

- Mining
- Oil and gas

Applications

- Signalling/Positioning
- Operating of heavy machinery
- Loading and hauling
- Hydraulic repair
- Shipping and loading of product
- Vehicle Maintenance
- General pumping work
- Preparation of site - set-up and disassembly of tool string
- Set-up of pressure manifold and tubing injector head
- Handling of tools
- Valve - line maintenance and repair
- Handling jagged metal
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Heavy machine operation

Key Features

- High-visibility on back-of-the-hand and palm side to increase safety over traditional high-visibility liner gloves
- Retro-reflective logo on back-of-the-hand to enhance safety in dark/low-light conditions
- 13-gauge liner offers excellent comfort and all day wear and is not sweaty compared to leather. Ergonomically designed forms provide naturally curved, relaxed fit to reduce hand fatigue
- Excellent dexterity enhances ability to pick up small items
- Provides excellent wet and dry grip
- Also available in vend pack

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
ActivArm® 97-013	Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Fiber glass, Polyester Cuff Style: Knitwrist	13	7, 8, 9, 10, 11	230-270 mm/ 9.05-10.63 inches	Orange	• 12 pairs in a bag; 6 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.