S4020

4

NONE

2-16-70

APPROVED B JM SUPERSEDED OR VOID DATA

USE OF

WE CAN ASSUME NO RESPONSIBILITY FOR

WITHOUT NOTICE

TOLERANCE AND CHANGE

TO MANUFACTURERS

MEMBER OF MORRIS GROUP INTERNATIONAL POST OFFICE BOX 3237
MONTGOMERY, ALABAMA 36109-0237 (USA) TEL: 334-277-8520 FAX: 334-272-7396 www.jrsmith




LOCATION

FINISHED FLOOR CLEANOUTS WITH "TWIS-TO-FLOOR®" ADJUSTABLE TOPS

ROUND NICKEL BRONZE TOP

FUNCTION: For use in finished floors bearing foot and medium load wheeled traffic. Allows for easy floor level adjustment.



TWIS-TO-FLOOR® ADJUSTMENT

NO-HUB OUTLET

NOTE: For applications using core drilling, the largest diameter of the cleanout assembly is 6 5/16"(160).

"A" (Pipe Size) = 02(50), 03(75), 04(100) or 05(125)

Fig. 4020S.....Gasket Seal - ABS Plug
Fig. 4021S.....Gasket Seal - Bronze Plug
Fig. 4023S.....Taper Thread - Bronze Plug
Fig. 4024S.....Taper Thread - ABS Plug

(Twis-to-Floor® design shown with gasketed plug.)

REGULARLY FURNISHED:

Duco Cast Iron Cleanout with Round Adjustable Scoriated Secured Nickel Bronze Top. Closure Plug Type as Indicated By Figure Number Selected.

VARIATIONS:

Flashing Flange -F
Flange with Flashing Clamp -F-C
Carpet Clamping Type -X
Carpet Marker Type -Y

Carpet Marker Type -Y Vandal Proof Top -U Wide Flange (DX)

OPTIONAL MATERIALS:

Galvanized Cast Iron -G Polished Bronze Top -PB

NOTE: Dimensions shown in parentheses are in millimeters.

Revised Variations BW 11-20-09 RN WEIGHT VOLUME FIGURE NUMBER Addition to Variations Added Core-Drilling Note Corrected Clamp & Flange view]]]] M 12/18/08 BW POUNDS CUBIC FEET 12/17/04 07/26/02 CL **4020 SERIES** REV. DATE **DESCRIPTION** BY CKD. BY

S4020BS

⋖

NONE

5-5-06

APPROVED BY: **CEL**

СН СНЕСКЕ**D** ВУ:

DRAWN BY: **RN**

UMBER

VOID DATA

SUPERSEDED OR

Ę, USE

RESPONSIBILITY FOR

WE CAN ASSUME NO

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCE AND CHANGE WITHOUT NOTICE


DRAWING NUMBEF

LOCATION

FINISHED FLOOR CLEANOUTS WITH "TWIS-TO-FLOOR®" ADJUSTABLE TOPS

ROUND NICKEL BRONZE TOP

FUNCTION: For use in finished floors bearing foot and medium load wheeled traffic. Allows for easy floor level adjustment.



SPIGOT OUTLET▲

"A" (Pipe Size) = 06(150) & 08(200)

- ▲ Sized for Service Weight and/or NO-HUB.
- When Flange-F is specified Min. 1 1/8 (29) becomes 1 5/8 (41)

"TWIS-TO-FLOOR®" ADJUSTMENT

SPIGOT OUTLET▲

Fig. 4023S.....Taper Thread - Bronze Plug

REGULARLY FURNISHED:

Duco Cast Iron Cleanout with Taper Thread Bronze Plug and Round Adjustable Scoriated Secured Nickel

Bronze Top. Vandal Proof Top -U

VARIATIONS:

Flashing Flange -F Flange with Flashing Clamp -F-C

Carpet Clamping Type -X

Carpet Marker Type -Y

Wide Flange (DX)

OPTIONAL MATERIALS:

Galvanized Cast Iron -G Polished Bronze Top -PB

> NOTE: Dimensions shown in parentheses are in millimeters.

WEIGHT VOLUME FIGURE NUMBER POUNDS CUBIC FEFT DATE **DESCRIPTION** CKD. BY