



**ITEM NUMBER 21C004  
7" X 12" HORIZONTAL  
BAND SAW**



<b>FEATURES</b>	<b>ADVANTAGES</b>	<b>BENEFITS</b>
Steel and cast iron construction	Minimal deflection & vibration	Quiet operation Lower maintenance costs Improved accuracy
Step pulley drive train	4 speed step pulley drive covers all sawing requirements	Better efficiency & performance
Powertrain -Gear box utilizes a bronze worm gear and hardened worm shaft in an oil bath	Delivers a consistent SFPM to blade	Lower maintenance costs Longer blade life
Adjustable hydraulic down feed system with adjustable counter balance spring	Accurate fine feed control Smooth consistent feed rate	Extends blade life Improves accuracy of cut Lower cost per cut
Automatic shut off at the end of cut	Readies saw for set up of next cut	Greater operator convenience & safety
Adjustable ball bearing blade guides	Easily adjustable blade guides mounted ridged adjustable slide arms	Ensures proper blade alignment & support Delivers consistent accuracy Longer blade life
Chip brush & flood coolant system	Most effective way to remove chips for the blade & workpiece	Longer blade life Increased productivity Lower cost per cut
Rapid acting vise	Fast clamping action with conventional tightening Miter capabilities up to 45 degrees	Increased productivity & efficiency
Adjustable material work stop	Easily adjusts to workpiece length Accurately handles both long & short workpieces	Allows for accurate repetition of cuts Delivers consistent accuracy Increases throughput Lowers cost per cut
Castors	Provides for easy positioning of saw anywhere in the shop	Greater convenience & efficiency