



AD2240W1  
AD2241W1

## Dual (Ultrasonic and Passive Infrared)

24V DC, 33mA. Requires a CU300xx series control unit.

Description	Color	Single Circuit	Dual Circuit
		1 button	2 buttons
Selectable Manual/ Auto ON.	Black	<b>AD2240BK1</b>	<b>AD2240BK2</b>
	Gray	<b>AD2240GY1</b>	<b>AD2240GY2</b>
	Ivory	<b>AD2240I1</b>	<b>AD2240I2</b>
	Light Almond	<b>AD2240LA1</b>	<b>AD2240LA2</b>
	White	<b>AD2240W1</b>	<b>AD2240W2</b>
Manual ON (Vacancy).	Black	<b>AD2241BK1</b>	<b>AD2241BK2</b>
	Gray	<b>AD2241GY1</b>	<b>AD2241GY2</b>
	Ivory	<b>AD2241I1</b>	<b>AD2241I2</b>
	Light Almond	<b>AD2241LA1</b>	<b>AD2241LA2</b>
	White	<b>AD2241W1</b>	<b>AD2241W2</b>

Note: Wallplate sold separately. See page E-23 for technical specifications, coverage patterns and wiring schematics.



WS2000W  
WS1000W



WS1020NW  
WS1021NW

## Passive Infrared

Manual time delay adjustment.

Description	Color	Standard	with Nightlight	with Neutral	with Nightlight and Neutral
Manual adjusting; selectable manual/auto ON operation; dual-voltage 120/277V AC; multi-way capable.	Gray	<b>WS2000GY</b>	<b>WS2000NGY</b>	—	—
	Ivory	<b>WS2000I</b>	<b>WS2000NI</b>	<b>WS2004I</b>	<b>WS2004NI</b>
	Light Almond	<b>WS2000LA</b>	<b>WS2000NLA</b>	—	—
	White	<b>WS2000W</b>	<b>WS2000NW</b>	<b>WS2004W</b>	<b>WS2004NW</b>
Manual adjusting; selectable manual/auto ON operation; 120V AC only.	Ivory	<b>WS1000I</b>	<b>WS1000NI</b>	—	—
	Light Almond	<b>WS1000LA</b>	<b>WS1000NLA</b>	—	—
	White	<b>WS1000W</b>	<b>WS1000NW</b>	—	—
Manual adjusting; manual ON operation; 120V AC only.	Ivory	<b>WS1001I</b>	<b>WS1001NI</b>	—	—
	Light Almond	<b>WS1001LA</b>	<b>WS1001NLA</b>	—	—
	White	<b>WS1001W</b>	<b>WS1001NW</b>	—	—
Manual adjusting; auto ON operation; dual circuit; 120V AC only.	Gray	<b>WS1020GY</b>	<b>WS1020NGY</b>	—	—
	Ivory	<b>WS1020I</b>	<b>WS1020NI</b>	<b>WS1024I</b>	<b>WS1024NI</b>
	Light Almond	<b>WS1020LA</b>	<b>WS1020NLA</b>	<b>WS1024LA</b>	<b>WS1024NLA</b>
	White	<b>WS1020W</b>	<b>WS1020NW</b>	<b>WS1024W</b>	<b>WS1024NW</b>
Manual adjusting; manual ON operation; dual circuit; 120V AC only.	Gray	<b>WS1021GY</b>	<b>WS1021NGY</b>	—	—
	Ivory	<b>WS1021I</b>	<b>WS1021NI</b>	<b>WS1025I</b>	<b>WS1025NI</b>
	Light Almond	<b>WS1021LA</b>	<b>WS1021NLA</b>	<b>WS1025LA</b>	<b>WS1025NLA</b>
	White	<b>WS1021W</b>	<b>WS1021NW</b>	<b>WS1025W</b>	<b>WS1025NW</b>

Note: See page E-24 for technical specifications, coverage patterns and wiring schematics.



DT2000W

## Digital Timer

Description	Color	Catalog Number
DIP switch enable preset intervals for 2 and 4 hours. User adjustable up to 24 hours. 3-way capable, 960W @ 120V AC and 1200W @ 277V AC.	White	<b>DT2000W</b>



WSTA120

## Programmable Timer

Description	Color	Catalog Number
Wall Switch Programmable Timer with Astronomical Clock, Features 3 Interchangeable cover colors: Gray, Light Almond and White. Compatible in SP and 3-Way configurations, 120V AC, neutral wire required.	White	<b>WSTA120</b>



DT5030W

## Count Down Timers

Description	Color	30 Minutes:	60 Minutes:	12 Hours:
		OFF, 5, 10, 20, 30	OFF, 15, 30, 45, 60	OFF, 2, 4, 8, 12
1000W @ 120V AC and 1400W @ 277V AC.	Ivory	<b>DT5030I</b>	<b>DT5060I</b>	<b>DT5012I</b>
	Light Almond	<b>DT5030LA</b>	<b>DT5060LA</b>	<b>DT5012LA</b>
	White	<b>DT5030W</b>	<b>DT5060W</b>	<b>DT5012W</b>