NIST Traceable Thermistor Instruments

Cooper-Atkins thermistor instruments are calibrated by means of temperature, electrical, and/or resistance standards traceable to the United States Department of Commerce National Institute of Standards and Technology (NIST). Used in HVAC/R applications where IAQ (Indoor Air Quality) and accuracy of measurements are critical to healthy environmental indoor conditions and product safety such as hospitals, labs, schools, refrigeration of products and energy consumption.







TM99A-032

The industry standard for applications where only one temperature is read at a time. Features include: Min/Max memory, Hold, Auto Shut-off with an LCD backlight for dark environments. The TM99A includes a pouch and #1075 general purpose puncture probe.

Temperature Range: -40° to 302°F (-40° to 150°C)

Accuracy: $\pm 0.3^{\circ}F$ (0.2°C) or $\pm 0.5\%$ of reading whichever

is greater

Resolution: 0.1°

Regulatory Listings: CE, WEEE, RoHS

Warranty: 5 year instrument, 1 year probe

SH66A-E-032

The perfect choice for applications when multiple temperature measurements are needed. Features include: LCD backlight for dark environments; sealed keypad which protects the instrument from spills and dust; and a battery eliminator jack. It simultaneously measures suction and liquid line temperatures, temperatures across condensing coils, evaporator coils and ambient temperatures. View temperature differential between zones 1 and 2 and review min/max temperatures from all three zones. The SH66A-E-032 includes the #1075 general purpose probe, #2010 Air Probe and #4011 pipe strap probe.

Temperature Range: -40° to 300°F (-40 to 150°)

Accuracy: ±0.3°F (±0.2°C) or ±0.5% reading, whichever

is greater

Resolution: 0.1°

Regulatory Listings: CE, WEEE, RoHS
Warranty: 5 year instrument, 1 year probe

SRH77A-E-032

The experts choice when temperature and relative humidity measurements are critical since it is a fast and accurate tool. Features Include: LCD backlight for dark environments; sealed keypad which protects the instrument from spills and dust; and a battery eliminator jack. View temperature differential, % relative humidity, and wet-bulb. View temperature differential between zones 1 and 2 and review min/max temperatures from all three zones. The SRH77A-E-032 includes the #1075 general purpose puncture probe, #4011 pipe strap probe and #5028 slim humidity probe.

Temperature Range: -40° to 300°F (-40 to 150°C)

Accuracy: ±0.3°F (±0.2°C) or ±0.5% reading, whichever

is greater

Humidity Range: 10 to 95% RH

Humidity Accuracy: ±2% (from 20 to 80% RH)

±3% (below 20% and above 80%)

Resolution: 0.1°, 1% RH

Ambient Operating Range: 0° to 130°F (-18° to 54°C)

(90% RH non-condensing)

Regulatory Listings: CE, WEEE, RoHS Warranty: 5 year instrument, 1 year probe

ATKINS Accuracy to the Highest Degree

CERTIFICATE OF CALIBRATION & REPORT

Instrument Identification

Company: Customer A Instrument ID #:: 11413018
Description: Temperature Tester Model: TM99A
Mfr.: Cooper-Atkins Corporation Serial #: 11413018

Accuracy: ±0.3°F / ±0.2°C or ±0.5% of reading whichever is greater

Emissivity: N/A

Calibration Information

Technician: Employee A
Condition, As Found: NEW
Condition As Left: In Tolerance
Procedure: PS09-697

Date: January 14, 2013

Temperature: 74.7 Humidity: 25%

Five Year Instrument Warranty



Any instrument which proves to be defective in material or workmanship within five years of original purchase will be repaired or replaced without charge upon receipt. This Limited Warranty does not cover damage in shipment or failure caused by tampering, obvious carelessness or abuse, and is the purchaser's sole remedy.

