


I-Force® and I-Force Slim

ANSI • CE • CSA • AS • Ballistic •



Dual pane lens // Outer polycarbonate lens protects against the environment, while inner acetate lens prevents fogging // Outside lens is coated with anti-fog treatment // Quick release interchangeable temples and strap // Removable vented flame resistant foam carriage // Passes Ballistic MIL-PRF-32432 High Velocity Impact standards

I-Force Black Frame | 4 Variations

- SB7010SDT ••••• Clear Dual Pane H2X AF
- SB7020SDT ••••• Gray Dual Pane H2X AF
- SB7030SDT ••••• Amber Dual Pane H2X AF
- SB7080SDT ••••• I/O Mirror Dual Pane AF

I-Force Slim Black Frame | 3 Variations

- SB7010SDNT ••••• Clear Dual Pane H2X AF
- SB7020SDNT ••••• Gray Dual Pane H2X AF
- SB7080SDNT ••••• I/O Mirror Dual Pane AF



148 mm



157 mm



WATCH THE VIDEO
Vimeo.com/Pyramex/I-Force



i I-Force Slim is about 6% smaller than the I-Force.

I-Force General Specifications

Weight: 48 gm
PD: 68 mm
Bridge: 14.5 mm
Lens base: 8 curve
Lens size diagonal: 72 mm
Lens size vertical: 51 mm
Lens thickness: 1.8 mm
Overall length (lens - tip): 165 mm
Overall width (hinge - hinge): 165 mm
Closest point between lens: 16 mm

Materials

Lens: polycarbonate + acetate
Foam: chloroprene rubber foam
Nosepiece: chloroprene rubber foam
Front carriage: nylon
Foam frame: nylon
Goggle + Temple strap: polyester
Hinge: polycarbonate
Ratchet: polycarbonate
Temples: polycarbonate
Temple tips: nylon
Temple strap holder: nylon

I-Force Slim General Specifications

Weight: 47.5 gm
PD: 64 mm
Bridge: 14.5 mm
Lens base: 8 curve
Lens size diagonal: 67 mm
Lens size vertical: 51 mm
Lens thickness: 1.8 mm
Overall length (lens - tip): 160 mm
Overall width (hinge - hinge): 144 mm
Closest point between lens: 16 mm

Part No.	Lens Marking	Temple Marking
SB7010SDT	P Z87+U6 L1.3 X	P Z87 + / P c SEI Z94.3
SB7020SDT	P Z87+ U6 L2.5 X	P Z87 + / P c SEI Z94.3
SB7030SDT	P Z87+S X	P Z87 + / P c SEI Z94.3
SB7080SDT	P Z87+U6 L1.7 X	P Z87 + / P c SEI Z94.3
SB7010SDNT	P Z87+U6 L1.3 X	P Z87 + / P c SEI Z94.3
SB7020SDNT	P Z87+ U6 L2.5 X	P Z87 + / P c SEI Z94.3
SB7080SDNT	P Z87+U6 L1.7 X	P Z87 + / P c SEI Z94.3

Lens Marking Symbols

P: Manufacturer's mark
Z87: ANSI standard for eye and face protection devices
+: High impact
S: Special Purpose
X: Tested Anti-fog

UV Filter Transmittance

U6: .01% max effective far UV • .1% max near UV

Visible Light Filters

L1.3: 85% Max. Visible Light
L1.7: 55% Max. Visible Light
L2.5: 29% max visible light

Temple Marking Symbols

P: Manufacturer's mark
Z87: ANSI standard for eye and face protection devices
+: High impact
c SEI Z94.3: CAN/CSA standard for eye and face protection devices