

**Provoq®** ANSI • CSA •



Soft nosepiece // Rubber temples



SP72

**Pink Temples | 1 Variation**

- SP7210ST • Clear AF

**Black Temples | 11 Variations**

- S7210S •• Clear
- S7210ST •• Clear AF
- S7220S •• Gray
- S7220ST •• Gray AF
- S7230S •• Amber
- S7255S • Multi-Color Mirror
- S7260S • Infinity Blue
- S7270S •• Silver Mirror
- S7275S •• Blue Mirror
- S7280S •• I/O Mirror
- S7280ST • I/O Mirror AF

Part No.	Lens Markings	Frame Markings	General Specifications	Materials
S7210S	P Z87 + U6	P Z87 + / P c SEI Z94.3	Weight: 24.9 gm	Lens: polycarbonate
S7210ST	P Z87 + U6	P Z87 + / P c SEI Z94.3	PD: 64 mm	Temples: polycarbonate
S7220S	P Z87 + U6 L3	P Z87 + / P c SEI Z94.3	Bridge: 16.66 mm	Hinge: polycarbonate
S7220ST	P Z87 + U6 L3	P Z87 + / P c SEI Z94.3	Lens base: 9 curve	Screw: plated steel
S7230S	P Z87 + S	P Z87 + / P c SEI Z94.3	Lens size diagonal: 79.83 mm	Temple Tip: thermoplastic rubber
S7255S	P Z87 + S	P Z87 +	Lens size vertical: 41.12 mm	Nosepiece: thermoplastic rubber
S7260S	P Z87 + S	P Z87 +	Lens thickness: 2.4 mm	
S7270S	P Z87 + S	P Z87 + / P c SEI Z94.3	Overall length (lens - tip): 158 mm	
S7275S	P Z87 + S	P Z87 + / P c SEI Z94.3	Overall width (hinge - hinge): 136 mm	
S7280S	P Z87 + U6 L1.7	P Z87 + / P c SEI Z94.3	Closest point between temple tips: 79.35 mm	
S7280ST	P Z87 + U6 L1.7	P Z87 +	Closest point between lens: 8.18 mm	
SP7210ST	P Z87 + U6	P Z87 +		

**Lens Marking Symbols**

P: Manufacturer's mark  
 Z87: ANSI standard for eye and face protection devices  
 +: High impact  
 S: Special Purpose  
 UV Filter Transmittance  
 U6: .01% max effective far UV • .1% max near UV  
 Visible Light Filters  
 L1.7: 55% max visible light  
 L3: 18% max visible light

**Temple Marking Symbols**

P: Manufacturer's mark  
 Z87: ANSI standard for eye and face protection devices  
 +: High impact  
 c SEI Z94.3: CAN/CSA standard for eye and face protection devices