

V2G-Plus™



- Includes a wide adjustable elastic strap with quick release system for secure fit.
- TPU frame features excellent resistance to cold and heat.
- Thermo Lens System provides excellent resistance to fogging caused by temperature difference between indoor and outdoor or between on-site and ambient environment.
- Special indirect ventilation system located at the top and bottom of frame allow air flow and heat release.
- Multi-functional goggle with 180° vision, protects against chemical splash, sun glare, dust, flying particles, wind.

- Outer polycarbonate lens protects against the environment, while an inner lens prevents fogging.
- Inner lens is made from acetate, separated by a thin spacer of air, sealed together with foam.
- Scratch resistant polycarbonate lens provides 99% UVA/B/C protection.
- Passes MIL-PRF 32432 High Velocity Impact Standards.
- Passes D3: Droplet & Splash Test – provides protection from droplets and splashes.



1/box 144/case

Black Goggle with Strap

Part

GB6410SDT • • • • •

GB6420SDT • • • • •

Lens

 Clear H2X Anti-Fog Dual Lens

 Gray H2X Anti-Fog Dual Lens



1/box 300/case

RX6400

V2G-Plus Rx Insert

Optional RX-insert frame secures in the inner side of frame.

NOTE: Take insert to local optometrist for Rx lens installation.