

Product data sheet

Characteristics

8903SPG11V02

Contactor, Type S, multipole lighting,
mechanically held, 60A, 3 pole, 110/120VAC
50/60Hz coil, NEMA 1



Main

| | |
|---------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type | S |

Complementary

| | |
|-------------------------|----------------------------------|
| Control Circuit Voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Current Rating | 60 A |
| Number of Poles | 3P |
| Control Units | No control units |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | Without |
| Other Options | None |
| Electrical Connection | Lugs |
| Height | 14.13 in (359 mm) |
| Depth | 9.72 in (247 mm) |
| Width | 8.11 in (206 mm) |

Environment

| | |
|------------------------|---|
| Enclosure Type | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-----------------------|--------------------------------|
| Category | 21324 - 8903 S (NOT S°C) MECH. |
| Discount Schedule | CP1 |
| GTIN | 785901102595 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 20.18 lb(US) (9.154 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 10.80 in (27.432 cm) |
| Package 1 width | 10.50 in (26.67 cm) |
| Package 1 Length | 16.70 in (42.418 cm) |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not compliant |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|