

# Brighten



Application illustration only, subject lamps not used in photo.

## LED commercial indoor/outdoor PAR38 lamps

For indoor and outdoor applications, GE offers a multitude of wattage options with a high light output.

### LOW-COST OPERATION

- For example, using only 26 watts of energy, save over \$517 in energy costs over the rated life of the lamp versus a standard 120-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources
- Ideal for both indoor and outdoor applications
- UL wet rated for outdoor applications

### EXCELLENT COLOR RENDERING

- Available with a CRI of 82 - 84

### COLOR TEMPERATURE

- Halogen-like color
- Available in 2500K, 2700K, 3000K, 3500K, 4000K and 5000K

### LONG LIFE

- Up to 25,000 hours rated life (L70)

### DIMMABLE

- Dims from 100% to 10%

### BEAM PATTERNS

- Available in 12°, 15°, 25°, 35° and 40° beam patterns

### ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient and contain no lead or mercury

### GE QUALITY AND RELIABILITY

- 3-year limited warranty

ecomagination<sup>SM</sup>

To learn more about saving money and energy, go to: <http://products.currentbyge.com>.


Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

**current**  
powered by GE




# LED commercial indoor/outdoor PAR38 lamps


## Directional Lamps (PAR)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
PAR38 - Low Glare - Visual Comfort Lens™																		
	MED	12	92971	LED12D38W3827/40	120	6	5.31	1050	2300	2700	81	100W	25,000	Yes	★	Damp	Flood, 40° beam, White	
			92972	LED12D38W3830/25	120	6	5.31	1050	5500	3000	81	100W	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White	
			92973	LED12D38WO3830/40	120	6	5.31	1050	2300	3000	80	100W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			24520	LED12D38W3930/12	120	6	5.31	950	15000	3000	90	90W	25,000	-	-	Damp	Spot, 12° beam, White	
		18	92950	LED18D38W3827/25	120	6	5.12	1550	5800	2700	81	120W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			92923	LED18D38W3927/25	120	6	5.31	1250	4900	2700	92	100W	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White	
			92958	LED18D38W3827/40	120	6	5.12	1550	3800	2700	81	120W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			92926	LED18D38W3927/40	120	6	5.12	1250	2900	2700	92	120W	25,000	Yes	★	Damp	Flood, 40° beam, White	
			92927	LED18D38W3930/15	120	6	5.32	1350	15000	3000	92	75W	25,000	Yes	★	Wet	Spot, 15° beam, White	
			92961	LED18D38W3830/15	120	6	5.12	1750	20000	3000	81	150W	25,000	Yes	★	Wet	Spot, 15° beam, White	
			92963	LED18D38W3830/25	120	6	5.12	1550	6000	3000	81	120W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			92933	LED18D38W3930/25	120	6	5.31	1350	5200	3000	92	100W	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White	
			92967	LED18D38W3830/40	120	6	5.12	1550	4000	3000	81	150W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			92934	LED18D38W3930/40	120	6	5.12	1350	3200	3000	92	120W	25,000	Yes	★	Damp	Flood, 40° beam, White	
			85085	LED18D38W3835/25	120	6	5.31	1700	6500	3500	81	120W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			87917	LED18D38W3835/40	120	6	5.31	1700	4400	3500	81	150W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			93171	LED18D38W3840/25	120	6	5.31	1700	6500	4000	81	120W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			93172	LED18D38W3840/40	120	6	5.31	1700	4400	4000	81	150W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			65730	LED18D38W3850/25	120	6	5.31	1700	6500	5000	81	120W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			65731	LED18D38W3850/40	120	6	5.31	1700	4400	5000	81	150W	25,000	Yes	★	Wet	Flood, 40° beam, White	

## Directional Lamps (PAR38 - High Output)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
Single Optics																		
		32	75447	LED32DP38W830/15	120	6	5.12	3000	26000	3000	82	250W	25,000	Yes	★	Wet	Spot, 15° beam, White	
			88801	LED32DP38W830/25	120	6	5.12	3000	13000	3000	80	250W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			88810	LED32DP38W830/40	120	6	5.12	3000	6000	3000	80	250W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			30233	LED32DP38W835/15	120	6	5.12	3100	25000	3500	80	250W	25,000	Yes	★	Wet	Spot, 15° beam, White	
			30237	LED32DP38W835/25	120	6	5.12	3100	13000	3500	80	250W	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
			30239	LED32DP38W835/40	120	6	5.12	3100	6000	3500	80	250W	25,000	Yes	★	Wet	Flood, 40° beam, White	
			20109	LED32P38W830/15	120-277	6	5.12	3000	25000	3000	80	250W	25,000	-	★	Wet	Spot, 15° beam, White	
			20130	LED32P38W830/25	120-277	6	5.12	3000	13000	3000	80	250W	25,000	-	★	Wet	Narrow Flood, 25° beam, White	
			20137	LED32P38W830/40	120-277	6	5.12	3000	6000	3000	80	250W	25,000	-	★	Wet	Flood, 40° beam, White	

## Directional Lamps (PAR38- Value)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
Single Optics																		
	PAR38	MED	11	91360	LED11P38W830/25	120	6	5.04	950	4000	3000	90W	10,000	-	-	Wet	Flood, 25° beam, White, STIR	
			15	32213	LED15DP38W830/40	120	6	5.04	1300	2300	3000	81	90W	25,000	Yes	★	Wet	Flood, 40° beam, White, STIR

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

\* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

\*\* Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

# UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "TTP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks



<http://products.currentbyge.com>

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2018 GE.

63555 (Rev 04/24/18)

