



Main

Range	TeSys
Product name	TeSys GB2
Device short name	GB2
Product or component type	Circuit breaker
Device application	Control
Poles description	1P
Network type	AC/DC
Utilisation category	Category A IEC 60947-2 DC-12 IEC 60947-5-1 DC-13 IEC 60947-5-1
Network frequency	50/60 Hz IEC 60947-2
Breaking capacity	50 kA I _{cu} 110 V AC 50/60 Hz IEC 60947-2 50 kA I _{cu} 230/240 V AC 50/60 Hz IEC 60947-2 1.5 kA I _{cu} 24 V DC IEC 60947-2 1 kA I _{cu} 48 V DC IEC 60947-2
[I _{cs}] rated service short-circuit breaking capacity	25 % 230/240 V AC 50/60 Hz IEC 60947-2 50 % 110 V AC 50/60 Hz IEC 60947-2
Trip unit technology	Thermal-magnetic
Magnetic tripping current	14 A

Complementary

Mounting mode	By clips
Mounting support	Plate Rail
Mounting position	Horizontal Vertical
Control type	Toggle
Line Rated Current	1 A

[Ue] rated operational voltage	250 V AC 50/60 Hz IEC 60947-2 277 V AC 60 Hz CSA C22.2 No 235 277 V AC 60 Hz UL 1077 48 V DC
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-2
Power dissipation per pole	2 W
Mechanical durability	8000 cycles
Electrical durability	8000 cycles
Connections - terminals	connector 1 0.00...0.01 in ² (0.75...6 mm ²)solid without cable end connector 2 0.00...0.01 in ² (0.75...4 mm ²)solid without cable end connector 1 0.00...0.01 in ² (0.75...4 mm ²)flexible with cable end connector 2 0.00...0.00 in ² (0.75...2.5 mm ²)flexible with cable end
Tightening torque	10.62 lbf.in (1.2 N.m) connector
Mechanical robustness	Shocks 22 Gn for 20 ms IEC 60068-2-27 Vibrations 5 Gn, 5...110 Hz IEC 60068-2-6
Quantity per set	Set of 6
9 mm pitches	2
Height	2.91 in (74 mm)
Width	0.59 in (15 mm)
Depth	2.64 in (67 mm)

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-2 CSA C22.2 No 235 UL 1077
Product certifications	UL CSA
Protective treatment	TC
IP degree of protection	IP20 IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Operating altitude	9842.52 ft (3000 m)

Ordering and shipping details

Category	22631 - TELE CIRCUIT BREAKER (GB2)
Discount Schedule	I
GTIN	00785901214663
Package weight(Lbs)	0.05 kg (0.11 lb(US))
Returnability	Yes
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------
