

Power Strips used within the Patient Care Vicinity, may be permanently attached by a means such that it is only removable with the use of a tool. Choose the PSCLAMP for a safe & secure mounting solution.

For Patient-Care Vicinity – UL 60601-1 Medical-Grade Power Strip, 4 15A Hospital-Grade Outlets, Safety Covers, 15 ft. Cord

MODEL NUMBER: **PS-415-HGULTRA**



Full 60601-1 compliance, integrated locking safety covers and a 15 ft. cord make this medical-grade power strip ideal for all areas inside and outside of patient care vicinities.

Description

The PS-415-HGULTRA Medical-Grade Power Strip -- patent # 7,375,939 -- is the first power strip with full 60601-1 compliance and agency listing, making it ideal for standalone use in all patient care vicinities. This 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

A patented protection circuit guards against shock hazards by preventing power from reaching the unit's outlets in the presence of a fault. The protection circuit automatically resets itself and restores power once the fault threat is gone.

Anti-Microbial Protected with EPA Registered and FDA Compliant Silver Ionic Technology known to inhibit growth of Microbes on surfaces.

Mounting tabs and flanges let you install the PS-415-HGULTRA on a wide variety of surfaces. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

With a switchless design that prevents accidental shutoff and a 15-foot power cord that can reach a distant power source, the PS-415-HGULTRA is a recommended replacement for all non-compliant power strips.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for standalone use in patient-care vicinities, therapy rooms, imaging environments and administrative areas Patented protection circuit guards against shock hazards with automatic site fault protection Circuit breaker resets itself once fault threat is gone 120V, 50/60 Hz power strip complies with UL 60601-1 and UL 60950-1 specifications Patent # 7,375,939

Versatile Medical-Grade Solution 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power 15 ft. power cord provides ample reach to the power source Rugged all-metal housing for long life in

Highlights

- Approved for standalone use in all patient-care vicinities
- Complies with UL 60601-1 and UL 60950-1 specifications
- Patented protection circuit guards against shock hazards
- 4 NEMA 5-15R-HG hospital-grade outlets with locking safety covers
- 15 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Exclusive, patented anti-microbial coating - 99.9% effective in inhibiting bacteria and viruses

Package Includes

- PS-415-HGULTRA UL 60601-1 Medical-Grade Power Strip
- Owner's manual with maintenance requirements



demanding environments

Premium Safety Features Integrated locking outlet safety covers block access to unused outlets Built-in 15A circuit breaker protects against dangerous overloads Switchless design prevents accidental shut-off
Ready to Use Right Out of the Box Built-in mounting tabs and flanges for easy installation on a variety of surfaces

Exclusive, Patented Antimicrobial Protection Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria like C. diff and MRSA Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Specifications

OVERVIEW	
UPC Code	037332128430
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	Yes
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Anti-Microbial Protected	Yes
Color	White
Color (AC Line Cord)	White
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 334.01mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	92mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	5.59 x 14.73 x 36.58
Shipping Dimensions (hwd / in.)	2.20 x 5.80 x 14.40
Shipping Weight (kg)	1.63
Shipping Weight (lbs.)	3.60
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	1.45
Unit Weight (lbs.)	3.20
CERTIFICATIONS	
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)
Patented	Patent # 7,375,939
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>