

# PC 460

**Shurtape®**  
TRUE TO YOUR WORK™

## SHURGRIP® UTILITY GRADE, CO-EXTRUDED CLOTH DUCT TAPE

### TYPICAL APPLICATIONS

- For non-critical, general use in packaging, bundling, sealing, repairing, holding and waterproofing
- Also used in the remediation/abatement industry as a gooseneck tape

### PRODUCT FEATURES

- Good conformability
- Will not twist or curl during application
- Made using Polybonded CO-EX Technology®

### CONSTRUCTION

Overall Grade/Function: Utility

Backing: Waterproof polyethylene film with a cloth carrier

Adhesive: Natural rubber

### STANDARD WIDTH(S)

48 mm    72 mm

### STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



### PHYSICAL PROPERTIES    STANDARD    METRIC

Tensile Strength	17 lbs/in width	29.7 N/10 mm
Adhesion to Stainless Steel	86 oz/in width	9.41 N/10 mm
Thickness	6 mils	0.15 mm
Elongation	20%	20%
Service Temperature Range	40 F to 200 F	4 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

