



LADDER CABLE TRAY SYSTEM

90° Horizontal Elbow [9F]



Note: Use Adjustable Connectors for odd angles. Nominal 9" rung spacing maintained through centerline of all fittings.

CSA Certified for CSA Systems

Radius - R	Width - W	"A" Dimension	Part Number
12" (305mm)	6" (152mm)	15" (381mm)	XXX-069F-12
	9" (229mm)	16½" (419mm)	XXX-099F-12
	12" (305mm)	18" (457mm)	XXX-129F-12
	18" (457mm)	21" (533mm)	XXX-189F-12
	24" (610mm)	24" (610mm)	XXX-249F-12
	30" (762mm)	27" (686mm)	XXX-309F-12
	36" (914mm)	30" (762mm)	XXX-369F-12
	42" (1067mm)	33" (838mm)	XXX-429F-12
	48" (1219mm)	36" (914mm)	XXX-489F-12
24" (610mm)	6" (152mm)	27" (686mm)	XXX-069F-24
	9" (229mm)	28½" (724mm)	XXX-099F-24
	12" (305mm)	30" (762mm)	XXX-129F-24
	18" (457mm)	33" (838mm)	XXX-189F-24
	24" (610mm)	36" (914mm)	XXX-249F-24
	30" (762mm)	39" (991mm)	XXX-309F-24
	36" (914mm)	42" (1067mm)	XXX-369F-24
	42" (1067mm)	45" (1143mm)	XXX-429F-24
	48" (1219mm)	48" (1219mm)	XXX-489F-24
36" (914mm)	6" (152mm)	39" (991mm)	XXX-069F-36
	9" (229mm)	40½" (1029mm)	XXX-099F-36
	12" (305mm)	42" (1067mm)	XXX-129F-36
	18" (457mm)	45" (1143mm)	XXX-189F-36
	24" (610mm)	48" (1219mm)	XXX-249F-36
	30" (762mm)	51" (1295mm)	XXX-309F-36
	36" (914mm)	54" (1372mm)	XXX-369F-36
	42" (1067mm)	57" (1448mm)	XXX-429F-36
	48" (1219mm)	60" (1524mm)	XXX-489F-36

Prefix No.

[F] [D] [M] - [W] [Bp] - [R]

[F] Flange - (2=13/16", 4=1-1/4")

[D] Load Depth - (3", 4", 5", 6")

[M] Material/Finish - (6=Mill-Galv, 7=HDAF, 8=Alum., T=304SS)

[W] Width - (06", 09", 12", 18", 24", 30", 36", 42", 48")

[Bp] Basic Part No - 9F

[R] Radius - (12", 24", 36")

EXAMPLE: 238-129F-12

MATERIAL & FINISH SPECIFICATIONS (Ladder Cable Tray) – Siderails: Mill-Galvanized Steel [6] ASTM A-653-G90 CS (18 & 16 Gage); ASTM A-653-G90 CS (14 & 12 Gage) Hot-Dip Galvanized after Fabrication ASTM A-123 [7] ASTM A-1008 (18 & 16 Gage); ASTM A-1011 (14 & 12 Gage) Aluminum [8] AA-6063-T6 Extruded Type 304 Stainless Steel [T] ASTM A-240; Type 304 Rungs: Mill-Galvanized Steel [6] ASTM A-653-G90 CS Hot-Dip Galvanized after Fabrication ASTM A-123 [7] ASTM A-1008 Aluminum [8] AA-6063-T6 Extruded; AA-6063-T832 Extruded; AA-6063-T52 Extruded Type 304 Stainless Steel [T] ASTM A-269; Type 304

Project: _____

Approval Stamp:

Architect / Engineer: _____

Date: _____ Phone: _____

Contractor: _____

Address: _____

Notes 1: _____

Notes 2: _____