

HIGH PERFORMANCE IN FRIGID CONDITIONS

COLD TEMPERATURE CARTON SEALING TAPES

You expect that your carton sealing tape will perform reliably and maintain its hold – even in harsh, cold conditions. It's why Shurtape offers carton sealing tapes specifically formulated for high performance in frigid environments. So, you get the strong hold you need, without lowering your expectations for product performance just because the temperature drops.

Shurtape cold temperature carton sealing tapes are designed to provide an instant, permanent bond for light- to medium-weight cartons. Our HP Series cold temperature tapes offer an easy-release formula that won't slow you down in high-speed applications; while our AP Series cold temperature tapes make quick work of sealing cartons in manual packaging applications.





Shurtape cold temperature tapes are ideal for applications where the packaging environment falls below 35 F: frozen foods, meat and poultry processing, dairy facilities, and unheated warehouses and storage facilities in cold weather climates.

No matter the job or environment, you can trust Shurtape cold temperature tapes to get the job done.



HIGH PERFORMANCE IN FRIGID CONDITIONS

COLD TEMPERATURE CARTON SEALING TAPES

		Tensile	Adhesion to Stainless Steel	Thickness	Elongation
HP 132®	 <p>Automated or manual sealing of lightweight cartons</p> <ul style="list-style-type: none"> • High performance in cold temperature environments • Instant, permanent bond in subfreezing temperatures • Special release coating for consistent, low force unwind off the roll • Application temperature range of 20 F to 75 F • Service temperature range of -20 F to 100 F 	21 lbs/in width	30 oz/in width	1.6 mils	150%
HP 232®	 <p>Automated or manual sealing of medium-weight cartons</p> <ul style="list-style-type: none"> • High performance in cold temperature environments • Instant, permanent bond in subfreezing temperatures • Special release coating for consistent, low force unwind off the roll • Application temperature range of 20 F to 75 F • Service temperature range of -20 F to 100 F 	27 lbs/in width	30 oz/in width	1.9 mils	150%
AP 180®	 <p>Automated or manual sealing of lightweight cartons</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	20 lbs/in width	21 oz/in width	1.8 mils	150%
AP 201®	 <p>Automated or manual sealing of light- to medium-weight cartons</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	24 lbs/in width	22 oz/in width	2 mils	150%

For heavy duty cold temperature applications use AP 301® or AP 401®.



SHURTAPE.COM
1.888.442.TAPE



Shurtape®
TRUE TO YOUR WORK™

ISO 9001 CERTIFIED QUALITY SYSTEM © 2015 Shurtape Technologies, LLC
Printed in USA on recycled paper. Form #SS-CT Packaging SS-11/03/15-P500