

CP 743

Shurtape®
TRUE TO YOUR WORK™

SPECIALTY GRADE, PHOTOGRAPHIC BLACK MASKING TAPE

TYPICAL APPLICATIONS

- For use in photo studios, film processing labs and home dark rooms
- Recommended for use as a chart tape
- Used for quality photographic reproduction work, including cropping and edging negatives for contact printing
- Also used for sealing camera bellow and film holders against light leaks

PRODUCT FEATURES

- Very high adhesion
- Light-free masking
- Good quick stick
- Easy to unwind
- Highly conformable
- UV blocking
- Hand-tearable

CONSTRUCTION

Overall Grade/Function: Specialty, photographic masking

Backing: Impregnated paper

Adhesive: Rubber-based

STANDARD WIDTH(S)

24 mm 48 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

COLOR(S)



NATURAL
(NAT)

PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	24 lbs/in width	42.0 N/10 mm
Adhesion to Stainless Steel	47 oz/in width	5.14 N/10 mm
Thickness	6.5 mils	0.17 mm
Elongation	8%	8%
Service Temperature Range	45 F to 150 F	7 C to 66 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment.

Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

