


## 24-Outlet Power Strip with Industrial Surge Protector, 15-ft. Cord, 1650 Joules, 72 in. length

MODEL NUMBER: **SS7619-15**



### Highlights

- 24 outlets
- 15-ft. cord
- 72-in. length
- 1650-joule rating

### Package Includes

- SS7619-15 Power Strip/Surge Suppressor
- Set of adjustable mounting clips
- Warranty information
- Instruction manual

### Description

The SS7619-15 6-ft. power strip with AC surge suppression offers a convenient method of horizontal or vertical power distribution in equipment racks, computer rooms, workbenches, raceways and more. Includes 24 NEMA 5-15R output receptacles with 2.795-in. center-to-center spacing, 15-ft. AC line cord and adjustable mounting clips for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 1650 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15A resettable circuit breaker and attractive gray color scheme.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 24 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT: 6-ft. corded vertical/raceway power distribution strip

SURGE SUPPRESSION: 1650 joules

### Features

- Long 6-ft./72-in. strip offers convenient power distribution and surge suppression in equipment racks, computer rooms, workbenches, raceways and more
- Includes 24 NEMA 5-15R output receptacles with 2.795-in. center-to-center outlet spacing
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff with integrated 15 amp circuit breaker
- Adjustable mounting clips support installation in a variety of applications
- UL1363/1449 - 400V (USA), cUL (Canada)
- 15A power handling capacity with circuit breaker
- 1650-joule AC surge suppression
- 15-ft. AC line cord



## Specifications

OVERVIEW	
UPC Code	037332100283
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(24) 5-15R
Circuit Breaker (amps)	15
Outlet Spacing	2.795-in. (center to center)
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	22000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Combination AC circuit breaker and lighted two-position power switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1650
UL1449 Let Through Rating	400V UL Verified
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Anti-Microbial Protected	No
Color	Silver
Color (AC Line Cord)	Black
Included Mounting Accessories	Set of adjustable mounting clamps
Integrated Keyhole Mounting Slots	No
Material of Construction	Metal
Outlets Measurement (Center to Center)	69mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	6.10 x 8.13 x 191.77
Shipping Dimensions (hwd / in.)	2.40 x 3.20 x 75.50
Shipping Weight (kg)	2.54
Shipping Weight (lbs.)	5.60
Unit Dimensions (hwd / cm)	182.9 x 3.8 x 3.8
Unit Dimensions (hwd / in.)	72 x 1.5 x 1.5
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	No
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
Canada	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>