

# Miller DuraHoist™ Safety System

**New!**

*Two-piece mast offers various height options*

**Ideal for confined space and fall arrest applications in construction and general industry, including wastewater facilities**

- Provides flexibility to change overall system height from 41" to 146" (1.0m to 3.7m)
- Eliminates need for custom-length mast
- Provides additional solutions to height-restrictive applications than the DH-3 one-piece mast alone
- Constructed of high-strength, lightweight aluminum for easy transport and setup
- Provides 5,000 lbs. (22.2 kN) capacity anchor point
- Flush Floor Mount Sleeve eliminates the potential trip hazard presented by other floor mount sleeves



**DH-21/**  
12"-29" (.3m-.7m)  
Adjustable  
Offset – Upper Mast

**DH-22/21**  
21" (.5m) Lower  
Mast Extension



**DH-22/33**  
33" (.8m) Lower  
Mast Extension



**DH-22/45**  
45" (1.1m) Lower  
Mast Extension



**DH-22/57**  
57" (1.5m) Lower  
Mast Extension



**DH-20SS/**  
Flush Floor Mount  
Sleeve – Stainless Steel

Model No.	Description	Weight
DH-20ZP/	Flush Floor Mount Sleeve – Zinc Plated	21 lbs. (9.5kg)
DH-20SS/	Flush Floor Mount Sleeve – Stainless Steel	22 lbs. (10.0kg)
DH-21/	12"-29" (.3m-.7m) Adjustable Offset – Upper Mast	23 lbs. (10.4kg)
DH-22/21	21" (.5m) Lower Mast Extension	14 lbs. (6.4kg)
DH-22/33	33" (.8m) Lower Mast Extension	17 lbs. (7.7kg)
DH-22/45	45" (1.1m) Lower Mast Extension	20 lbs. (9.1kg)
DH-22/57	57" (1.5m) Lower Mast Extension	23 lbs. (10.4kg)

*This equipment should only be used in conjunction with the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.*



**Ask the Expert ... Ask Miller.**

800/873-5242  
or 814/432-2118

Fax 800/892-4078  
or Fax 814/432-2415

[www.millerfallprotection.com](http://www.millerfallprotection.com)



For more information or to place an order, please contact your Miller® distributor:

LMDTPM/0208/20M/RPI