

Product data sheet

Characteristics

9002AW5

Foot Switch, Harmony, industrial, unshielded, two stage, 5A at 600 VAC, SPDT contact each stage, NEMA 2, 4, 13 enclosure



Main

Range	9002AW
Product	Foot switch
Contact Operation	2 steps
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Unshielded
Operator Action	Spring return
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508
Height	3.90 in (99 mm)
Width	4.49 in (114 mm)
Depth	8.50 in (216 mm)

Ordering and shipping details

Category	21441 - 9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	785901816003
Nbr. of units in pkg.	1
Package weight(Lbs)	3.23 lb(US) (1.465 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.30 in (8.382 cm)
Package 1 width	4.80 in (12.192 cm)
Package 1 Length	9.00 in (22.86 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
