
## RATCHET TRAILER STABILIZING JACK - LO-J-100

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\* ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STATIC CAPACITY: 100,000 LBS. LIFTING CAPACITY: 50.000 LBS.

MAXIMUM WORKING CAPACITY AT GRADE (%)

TOP CAP: 8" DIAMETER WHEEL SIZE IS Ø10" HANDLE LENGTH IS 20"

0.50% 1.00%

0.00%

DISTRIBUTOR'S NAME: FOR INTERNAL USE ONLY PROJECT SIGN OFF VESTIL MANUFACTURING **SALES** 

Signed:

Printed Name:

Α

Ρ Ρ

R

0

HANDLE-

\* 3D VIEW SHOWN

DATE: 11/1<u>9/2015</u> **B.NOTHNAGEL** 

[ ] As drawn

SALES: X SCALE: 1:10 FILE NAME:

[ ] As marked

**DIMENSION TOLERANCE ± 1/4"** I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS

REPRESENTED SATISFIES DESIGN AND DIMENSION

REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO

CONFIRM PRODUCT AND INSTALLATION
COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE

AND LOCAL REGULATIONS AND STANDARDS.

ANY MODIFIED UNITS ARE NON-RETURNABLE

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

Χ

ENG.

FAB.

1.50% | 2.00% | 2.50% | 3.00% | 3.50% | 4.00% 100,000 80,000 66,000 55,000 46,000 41,000 37,000 33,000 29,000 POWER

REFERENCE: QUOTED LEAD TIME: X OUOTF #

13-007-034

W.O.# X