

# HELIX®

Knit wrist helps prevent dirt and debris from entering the glove

Black palm coating hides dirt and soil

Ultimate dexterity and tactility

13-gauge aramid and steel blend shell

Seamless construction for enhanced comfort and breathability

Flexible foam nitrile palm coating provides superior grip and abrasion resistance



Launderable for extended life

## 2080 Helix® Series

### ATTRIBUTES:

<b>Shell:</b>	13G aramid/steel	
<b>Coating:</b>	Material:	Foam Nitrile
	Finish:	Smooth
	Weight:	Medium weight
	Breathability:	Fair
	Flexibility:	Good
	Grip:	Dry or oil
<b>Sizes:</b>	6/XS through 11/XXL	

### FEATURES:

Innovation intertwined with safety. That's the DNA of the Helix® Series. Helix® Series gloves are tightly knit with strong yet extremely dexterous fibers that offer industry-leading cut protection and abrasion resistance. A seamless series that answers the call of duty for most jobs, these high-comfort knit gloves feature consistent sizing and fit across the line, with a variety of palm coatings that can be used for everything from wet and oil situations to dry applications.

**REACH**  
COMPLIANT

REACH Compliant: Avoidance of substances classified as carcinogenic, mutagenic or reprotoxic, persistent, bioaccumulative or toxic.

### PROTECTION ZONES:

	<span style="background-color: #FFC000; padding: 2px;">Aramid Blend Shell</span>								
	<table border="0"> <tr> <td>ANSI/ISEA CUT</td> <td>GRAM SCORE</td> <td>CE</td> <td>EN 388</td> </tr> <tr> <td><b>A6</b></td> <td><b>3159</b></td> <td><b>4X42F</b></td> <td></td> </tr> </table>	ANSI/ISEA CUT	GRAM SCORE	CE	EN 388	<b>A6</b>	<b>3159</b>	<b>4X42F</b>	
	ANSI/ISEA CUT	GRAM SCORE	CE	EN 388					
	<b>A6</b>	<b>3159</b>	<b>4X42F</b>						
<table border="0"> <tr> <td>ANSI/ISEA PUNCTURE</td> <td>Meets the following performance levels of EN407:</td> </tr> <tr> <td><b>3</b></td> <td>5.2 Contact Heat    Level 1</td> </tr> </table>	ANSI/ISEA PUNCTURE	Meets the following performance levels of EN407:	<b>3</b>	5.2 Contact Heat    Level 1					
ANSI/ISEA PUNCTURE	Meets the following performance levels of EN407:								
<b>3</b>	5.2 Contact Heat    Level 1								

## HexArmor®

Call **1-877-MY ARMOR** or visit **hexarmor.com**

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.