

MIT200 series

Digital/Analog Insulation and Continuity Testers



- Insulation testing to 1000 MΩ
- Continuity testing at 200 mA down to 0.01 Ω
- Live circuit warning (voltage display) and test inhibit
- Digital/analog display
- Alkaline or rechargeable batteries
- 14 °F to 131 °F operating temperature
- CAT III 600 V
- Conforms to EN 61557

DESCRIPTION

The MIT200 is one of the most compact insulation testers available on the market today. With options of one, two and three test voltage instruments, the MIT200 series offers a surprising range of safety and operational features.

The display offers a combination of digital readout and analog display, using Megger's patented DART technology, so includes the benefits of an LCD display such as clear, accurate measurement and precise readings, with an analog pointer response for evaluating circuit charge and discharge characteristics.

The instrument housing is in tough ABS, designed to withstand the rigours of hard day-to-day use, and is small enough to drop into your pocket or toolbag.

Battery requirements are 6 AA batteries of either standard alkaline or nickel metal hydride (NiMH) rechargeable type. A low battery warning indicator gives advanced warning of exhausted batteries.

Continuity testing

Automatic continuity testing is performed at 200 mA to ensure compliance with international requirements. The convenient autostart feature means there is no need to press the test button to begin the test - both hands can be used to hold the test lead probes.

All instruments will measure up to 100 Ω on continuity, with 0-10 Ω using 200 mA so meeting international electrical testing requirements.

Lead null is possible up to 9.99 Ω of test lead resistance, providing the ability to null fused, extended or standard test leads.

Continuity buzzer

A buzzer provides a means of rapid cable testing and circuit continuity identification, with voltage protection should you accidentally touch a live circuit. The buzzer operates at a 2 Ω threshold.

Insulation testing

There are four instruments in the range offering range configurations shown in the table on page 2, providing an ideal entry-level solution to most low voltage insulation testing applications. Insulation test ranges include 250 V; 500 V and 1000 V depending on model. Auto discharge ensures all circuits under test are safely discharged after testing.

Note: the 1000 V insulation test range provides a high voltage warning prior to test voltage being applied.

Safety

Every Megger instrument is designed with safety as its primary objective. There are in-built safety checks to warn of inadvertent connection to a hazardous live supply on all ranges, and all instruments meet or exceed the requirements of safety directive IEC 61010 and EN 61557 for insulation and continuity testing.

Default volt meter

A built-in voltmeter is automatically activated and displays the system voltage when the instrument is connected to a circuit with an a.c. or d.c. voltage greater than 25 V.

Test inhibit

Circuits in excess of 25 V will generate a voltage warning as above. The instrument will inhibit testing on circuits over 50 V on both continuity and insulation test ranges, protecting the operator and the instrument from injury or damage.

600 V CAT III

The MIT200 series has been designed for use on applications up to 600 V CAT III.

APPLICATION

The MIT200 series will find applications when installing electrical installations, on both domestic and industrial systems, as well as within site maintenance and service departments.

The MIT200 series of insulation and continuity testers are also ideal for testing domestic appliances, power tools, transformers, motors, generators, switchgear, electrical panels etc., as well as fixed electrical wiring systems.

Their small size and light weight make them ideal for those engineers that need to carry an insulation tester for extended periods.

All instruments meet the requirements of most International Standards including VDE 0413 Part 1 and BS 7671 (the 17th Edition of the IEE Wiring Regulations).

FEATURES AND BENEFITS

- Meets the international requirements of EN 61557 for Insulation and Continuity testing.
- Display of insulation measurement up to 1000 M Ω on a combined analog arc and a digital display.
- Continuity range with 0.01 Ω resolution and a short circuit current in excess of 200 mA.
- Automatic continuity testing leaves both hands free. No need to press the test button.
- Automatic power-down if left unattended to preserve battery power.
- Automatic voltage detection and warning avoids accidental contact with hazardous live circuits.
- Test lead zero allows compensation for test lead resistance up to 10 Ω .

	MIT200	MIT210	MIT220	MIT230
Insulation testing				
250 V			■	■
500 V	■		■	■
1000 V		■		■
1000 M Ω range	■	■	■	■
Auto-ranging	■	■	■	■
Auto discharge	■	■	■	■
Test inhibit	■	■	■	■
Live circuit voltage display	■	■	■	■
Continuity testing				
Continuity at >200 mA	■	■	■	■
Continuity to 0.01 Ω	■	■	■	■
Test lead null (9.99 Ω)	■	■	■	■
Automatic continuity test	■	■	■	■
Continuity buzzer with 2 Ω threshold	■	■	■	■
Default volts warning	■	■	■	■
General				
Digital display + arc	■	■	■	■
Battery condition	■	■	■	■
Auto power down	■	■	■	■
Tough carry case	■	■	■	■
Test leads	■	■	■	■
CAT III 600 V	■	■	■	■
Environmental				
Operation temperature	+14 °F to +131 °F (-10 °C to +55 °C)			
Storage temperature	-4 °F to +149 °F (-20 °C to +65 °C)			
IP rating	IP40			

SPECIFICATIONS

Insulation range

Nominal test voltage: 1000 V, 500 V, 250 V (d.c.)


Measurement range: 10 k Ω - 1000 M Ω on all ranges
Terminal voltage on open circuit (d.c.):
-0 % +25 % of rated voltage

Test current on load:
>1 mA at minimum pass values of
insulation as specified in

BS 7671, HD 384, IEC 364 and
VDE 0413 part 1

Chart/graphic

Terminal characteristics



Continuity range

Measuring range: 0,01 Ω - 100,0 Ω
(0 -50 Ω on analog scale)

Open circuit voltage: 5 V \pm 1 V

Short circuit current: 205 mA +10 mA -5 mA
>18 mA (10 - 100 Ω)

Accuracy (at 20° C) \pm 0,01 Ω to 9.99 Ω \pm 3 % \pm 2 digits
10,0 Ω to 99.9 Ω \pm 5 % \pm 2 digits

Zero offset adjust: 0 to 9.99 Ω

Continuity buzzer Operates at < 2 Ω

Default voltmeter >25 V a.c. or d.c. is applied display will
operate as a voltmeter.

Range: 25 V to 600 V @ 50/60 Hz & d.c.
Accuracy: 25 V to 450 V a.c./d.c. \pm 1% \pm 1 digit
450 V to 600 V a.c. \pm 2% \pm 1 digit
Test inhibit If more than 50 V is detected, testing
will be inhibited.
Auto power down Auto power down operates after
10 minutes if left in standby mode.

Operating temperature range and humidity

-10 $^{\circ}$ C to +55 $^{\circ}$ C
93 % R.H. at +40 $^{\circ}$ C max.

Storage temperature range and humidity

-25 $^{\circ}$ C to +65 $^{\circ}$ C

IP rating

IP40

Fuse

500 mA (F) 600 V, 32 x 6 mm

Ceramic HBC 50 kA minimum.

Display shows if fuse is ruptured.

Over-voltage safety category

Meets the requirements of IEC61010- 1
Cat III 600 V phase to earth.

Automatic discharge

After an insulation test the item under
test will be discharged automatically.
Any voltage present will be indicated on
the display so that the discharge can be
monitored.

Power supply

Battery 6 x 1,5 V cells IEC LR6 type
(AA alkaline).

Rechargeable NiMH cells may be used.

Battery condition is constantly shown on
the display as a four section bargraph.

Battery life

3000 consecutive tests (5 seconds per test)
on any test using 2 Ah batteries.

Weight

All units: 1.17 lb (530 gms) \pm 5 %

Dimensions

All units: 7.7 x 3.8 x 1.6 in. (195 x 98 x 40 mm)

EMC

In accordance with IEC61326-1

ORDERING INFORMATION

Description	Order Code
500 V Insulation and continuity tester	MIT200-EN
1000 V Insulation and continuity tester	MIT210-EN
250 V / 500 V Insulation and continuity tester	MIT220-EN
250 V / 500 V / 1000 V Insulation and continuity tester	MIT230-EN
Included Accessories	
Test lead set and crocodile clips	1002-001
Carry case	1007-168

Optional accessories	Order Code
Test lead set and crocodile clips	1002-001
Fused test lead set (1 pair)	1002-015
Removable protective holster	1007-166
Carry pouch	6220-773

SALES OFFICE

Megger USA -
Valley Forge Corporate Center
2621 Van Buren Avenue, Norristown,
Pennsylvania, 19403, USA
T. 1-610 676 8500
F. 1-610-676-8610

MIT200_DS_US_V09

www.megger.com
ISO 9001

The word 'Megger' is a registered trademark

Megger [®]