

**STREAMLIGHT 2AA PROPOLYMER® XENON or LED**  
**ALKALINE BATTERY POWERED FLASHLIGHT**

**MARKET**

**APPLICATIONS:** Industrial, Occupational Safety, Fire & Rescue, Sporting Goods, Law Enforcement, Security, Hardware/Tool, Consumer

**DESCRIPTION:** The 2AA ProPolymer is an extremely durable, waterproof alkaline battery-powered flashlight. This light offers a push-button tailswitch for momentary and on-off operation.

**CASE MATERIAL:** Housing made from high impact super tough nylon offering exceptional durability. Rubber coated facecap resistant to impact and shock.

**DIMENSIONS:** Length: 6.30 in. (16.00 cm) Diameter: Major Diameter: 1.30 in. (3.30 cm)  
Body Diameter: 0.89 in. (2.26 cm)

**WEIGHT:** 3.6 oz (100 grams)\*

**LENS:** Unbreakable polycarbonate with scratch-resistant coating.

**LIGHT SOURCE:** Xenon - Gas filled bi-pin bulb in parabolic reflector module.  
LED - One (1) 0.5 Watt High-Flux LED, 30,000 hour lifetime in parabolic reflector module.

**LIGHT OUTPUT:** Xenon- Up to 4,500 Peak Beam candlepower. Bulb Rating: 9 lumens typical.  
LED Rating - 25 Lumens typical.  
Parabolic reflector produces a focused beam with optimum peripheral illumination.

**ON/OFF:** Push button tail switch.

**RUN TIME:** Xenon - Up to 4 hours continuous run.  
LED - 18 continuous hours at regulated intensity.

**BATTERY:** (2) 1.5V "AA" alkaline cells - included in package.

**FEATURES:** O-Ring sealed construction  
Dust and water ingress protected to IP57; in accordance with specification EN60529:1992  
Impact resistant housing - drop test verified  
LED - Solid state power regulation provides maximum light output throughout battery life  
Push button tail switch for On/Off

**APPROVALS\*\*:** Most models meet applicable European Community Directives. **CE**

**WARRANTY:** Limited lifetime warranty.

**OPTIONAL ACCESSORIES:** N/A

\* With battery (included in purchase)

\*\* See product for specific ratings.

**Assembled In The USA.**

Document #217