




STAINLESS STEEL RIGID CONDUIT

Features:

- Manufactured in Type 304 and 316 stainless steel to meet the demands of any corrosive environment
- Polished to a bright, easily maintainable finish that is modern, attractive, easy to clean and that also enhances the surface's resistance to pitting and bacterial corrosion
- Calbrite stainless steel rigid conduit is installed in the same way as any other metallic conduit, there are none of the labor-intensive procedures that come with PVC-coated installations, nor the complicated maintenance and repair procedures
- Standard NPT threads allow for trouble-free installations
- Approx. Heat Tolerance = -150°F to 1600°F
- Includes one coupling with each length purchased

Certifications and Compliances:

- UL / cUL 6A Listed
- UL file number _ E230584
- Article 344, "National Electrical Code" (NEC)
- CSA C22.1
- Canadian Electrical Code (CEC), Part 1, Standard for Electrical Installations
- NSF / ANSI 169 Certified



Applications:

Stainless conduit is specified in corrosive applications that exceed the limitations of aluminum, fiberglass, rigid steel, PVC, & PVC coated conduit. Calbrite's Type 304 and 316 UL-listed stainless steel conduit meets and exceeds current requirements for wash down and harsh / corrosive environments and satisfies the strictest mandates for plant cleanliness by various state agencies, and hundreds of common regulatory requirements.

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical
- Pulp & Paper Mills
- Marine & Coastal Facilities

Type 304 Part Number	Type 316 Part Number	Trade Size	Outside Diameter	Inside Diameter	Threads per Inch	Length w/o Coupling	Weight Per Feet (lbs.)
S40510CT00	S60510CT00	1/2"	0.840"	0.622"	14	9' 11-1/4"	0.82
S40710CT00	S60710CT00	3/4"	1.050"	0.824"	14	9' 11-1/4"	1.09
S41010CT00	S61010CT00	1"	1.315"	1.049"	11.5	9' 11"	1.61
S41210CT00	S61210CT00	1-1/4"	1.660"	1.380"	11.5	9' 11"	2.18
S41510CT00	S61510CT00	1-1/2"	1.900"	1.610"	11.5	9' 11"	2.63
S42010CT00	S62010CT00	2"	2.375"	2.067"	11.5	9' 11"	3.50
S42510CT00	S62510CT00	2-1/2"	2.875"	2.469"	8	9' 10-1/2"	5.59
S43010CT00	S63010CT00	3"	3.500"	3.068"	8	9' 10-1/2"	7.27
S44010CT00	S64010CT00	4"	4.500"	4.026"	8	9' 10-1/4"	10.08
S45010CT00	S65010CT00	5"	5.563"	5.073"	8	9' 10"	14.61
S46010CT00	S66010CT00	6"	6.625"	6.093"	8	9' 10"	18.97

All dimensions are for informational purposes only *Tolerances +/- 5%