

AVAILABLE THROUGH

**GRAINGER**

FOR THE ONES WHO GET IT DONE

GRAINGER.COM® | 1.800.GRAINGER

## PIG BUILD-A-BERM BARRIERS

**BEST  
SELLER!**



30PW78

Open-cell foam interior springs back into shape after you walk on it or roll over it with a hand cart.

30RF31

Install a 2" H barrier around machines to keep leaks and drips away from walkways.

**PIG EXCLUSIVE!**

### **PIG** Build-A-Berm Barrier — Configure a barrier to fit your leak-prone area.

- PIG Build-A-Berm Barriers can be constructed into a **semipermanent, high-visibility barrier** that's exactly the size and shape you need — indoors or out
- Pliable open-cell foam barrier **springs back into shape** after you walk or roll over it with light, wheeled equipment (see drive-over version on page 4)
- Durable, 18 oz. vinyl covering **resists oils, coolants and most chemicals**
- **Contain leaks and spills around your machinery** without building expensive cement curbs or cutting angle iron
- For best sealing results, **secure to a smooth, sealed surface**
- **Kit (30RF31, 30PW86) includes** straight sections, corners and Sili-Thane sealant; create any length or configuration
- ◆ **Helps you comply** with SPCC and Stormwater Regulations

#### Add these components to your layout:

- **Corners** let you create liquidproof junctions; join two Build-A-Berm sections at a 90-degree angle
- **Vented corner** prevents seam rupture by letting air escape during a cart driveover
- **Wall end** seals flush against the floor and wall for a seepage-free connection
- **Drain plug** lets you drain your barrier with any standard garden hose

#### Available in four heights!



1 1/2" H  
30PW82



2" H  
30PW78 or  
30PW84



4" H  
30PW76



6" H  
30PW80

AVAILABLE THROUGH

**GRAINGER**

FOR THE ONES WHO GET IT DONE

GRAINGER.COM® | 1.800.GRAINGER




Great for use around storage areas, battery charging stations, machinery or any other leak-prone areas.

1.5" High PIG® Build-A-Berm® Barrier				
Item #	Mfr. Item #	Name	Size	Unit
30PW86	PLR511	Kit	4.5"W x 50'L x 1.5"H	1/box
30PW86 Contents = 2 PIG® Build-A-Berm® Barriers • 6 Sili-Thane™ 803 Sealant Tubes 4 PIG® Build-A-Berm® Corners				
30PW82	PLR278	Straight Section	4.5"W x 15'L x 1.5"H	1/box
30PW83	PLR279	Corner	4.5"W x 6.75"L x 1.5"H	2/box
30PW74	PLR114	Wall End	4.5"W x 6"L x 1.5"H	2/box
2" High PIG® Build-A-Berm® Barrier				
Item #	Mfr. Item #	Name	Size	Unit
30RF31	PLR222	Kit	5.5"W x 50'L x 2"H	1/box
30RF31 Contents = 2 PIG® Build-A-Berm® Barriers • 6 Sili-Thane™ 803 Sealant Tubes 4 PIG® Build-A-Berm® Corners				
30PW78	PLR264	Straight Section	5.5"W x 15'L x 2"H	1/box
30PW79	PLR265	Corner	5.5"W x 7.25"L x 2"H	2/box
30PW71	PLR103	Vented Corner	5.5"W x 7.25"L x 2"H	2/box
30PW75	PLR117	Wall End	5.5"W x 3"L x 2"H	2/box
4" High PIG® Build-A-Berm® Barrier				
Item #	Mfr. Item #	Name	Size	Unit
30PW76	PLR258	Straight Section	7.25"W x 5'L x 4"H	2/box
30PW77	PLR263	Corner	7.25"W x 9.5"L x 4"H	2/box
30PW87	PLR512	Wall End	7.5"W x 10"L x 4"H	2/box
6" High PIG® Build-A-Berm® Barrier				
Item #	Mfr. Item #	Name	Size	Unit
30PW80	PLR276	Straight Section	9"W x 5'L x 6"H	2/box
30PW81	PLR277	Corner	9"W x 10.5"L x 6"H	2/box
30PW88	PLR513	Wall End	9"W x 11"L x 6"H	2/box

\*BEST SELLER

Patent 5,820,297



### Installation Accessories — You'll need these to build your Build-A-Berm.

- Use vinyl cement (45JW36) to **connect Build-A-Berm sections at seams**
- Use sealant (45GP06) to **secure your Build-A-Berm Barriers to the floor**; forms a one-part hybrid seal that is flexible and liquidtight (included with 30PW86 and 30RF31)



Industrial-Strength Vinyl Cement		
Item #	Mfr. Item #	Description
45JW36	PTY105	8 oz. can
Sili-Thane™ 803 Sealant		
(Specify Color: Black or White)		
Item #	Mfr. Item #	Description
45GP06	PTY340-WH	10.3 fl. oz. cartridge • 6/case
45GP20	PTY340-1-WH	10.3 fl. oz. cartridge • 1 each

NOTE: Each cartridge covers 25 ft. when applied .25"W x .125"D

### Simple installation

1. Cut to desired length with scissors or utility knife
2. Fit pieces together and secure to floor with silicone sealant (45GP06 sold above; use one tube per approx. 25 ft. of barrier)
3. Seal seams with industrial-strength vinyl cement (45JW36 sold above; installs approx. 10 connections)



AVAILABLE THROUGH

**GRAINGER**

FOR THE ONES WHO GET IT DONE

GRAINGER.COM® | 1.800.GRAINGER



30PW76 and 30PW77  
(sold on page 2)


45GP18  
Self-Rising Drive-Over Barrier

Easy access for pallet jacks,  
forklifts and drum trucks!


## **PIG** Build-A-Berm Self-Rising Drive-Over Barrier — Roll across this special gate section, and when a spill strikes, it rises to the occasion.

- Berm wall lays flat to allow forklifts, pallet jacks and drum trucks to drive over for **easy access to containment area**
- In the event of a spill, drive-over gate will **automatically rise with the spill level** to keep liquids contained
- Berm ends can be **directly connected** to an existing 4"H Build-A-Berm system (PLR258, sold separately on page 2)
- Ends of 4"H berm are pliable, open-cell foam core covered with vinyl; gate section is **constructed of durable PVC**
- Secure to a smooth, sealed surface with Sili-Thane sealant and reinforce with predrilled aluminum mounting strips and anchors; seal seams with Industrial-Strength Vinyl Cement (**sealant and vinyl cement sold separately on page 2**)

- ◆ **Helps you comply** with 40 CFR 112.7 SPCC Regulations
- ◆ **Helps you comply** with 40 CFR 122.26 Stormwater Regulations
- ◆ **Helps you comply** with 40 CFR 264.175



**Big leak? No worries!**  
Orange gate section rises with the liquid level for instant containment.

4" High PIG® Build-A-Berm® Self-Rising Drive-Over Barrier 				
Item #	Mfr. Item #	Name	Size	Unit
45GP18	PLR518	Drive-over Section	7"W x 9"L x 4"H	1/box

Patent Pending

AVAILABLE THROUGH

**GRAINGER**

FOR THE ONES WHO GET IT DONE

GRAINGER.COM® | 1.800.GRAINGER



**TOUGH ENOUGH FOR TRUCK TRAFFIC.**

**PIG Drive-Over Build-A-Berm Barrier — Build a spill berm that can handle heavy vehicle driveovers.**

- Provides **semipermanent containment** in high-traffic areas on concrete, asphalt or most sealed surfaces; for best results, use on a smooth, sealed surface
- Constructed of 40-ounce, vinyl-coated fabric with an open-cell foam core; compresses to approximately 1/4" when driven over; **springs back to shape when vehicles pass**
- Can withstand **indoor or outdoor traffic from heavy vehicles**
- Predrilled aluminum mounting strips with **anchors secure berm to most surfaces**; remove anchors to reposition and **create any configuration**
- **Vented corner** allows built-up air pressure caused by heavy vehicle driveovers to escape; **wall ends** seal flush for seepage-free connection
- ◆ **Helps you comply** with SPCC and Stormwater Regulations



1.5" High PIG® Drive-Over Build-A-Berm® Barrier				
Item #	Mfr. Item #	Name	Size	Unit
30PW89	PLR514	Straight Section	4.5"W x 12"L x 1.5"H	1/box
30PW90	PLR515	Vented Corner	4.5"W x 6.75"L x 1.5"H	2/box
30PW91	PLR516	Wall End	4.5"W x 6"L x 1.5"H	2/box
2" High PIG® Drive-Over Build-A-Berm® Barrier				
Item #	Mfr. Item #	Name	Size	Unit
30PW84	PLR283	Straight Section	5.5"W x 12"L x 2"H	1/box
30PW84 Contents • 6 Mounting Strips • 33 Anchors				
30PW72	PLR108	Vented Corner	5.5"W x 11.25"L x 2"H	2/box
30PW73	PLR109	Wall End	5.5"W x 3"L x 2"H	2/box

\*BEST SELLER

Patent 5,820,297



Sili-Thane 803 Sealant (45GP06, sold on page 2) cures fast and holds securely.



Use vinyl cement (45JW36, sold on page 2) to connect barrier sections and corners.

**"...made going over strips a walk in the park."**

"I work in a chemical warehouse where forklift traffic is constant. Build-A-Berm made going over containment strips a walk in the park. I like this product so much that I installed it in our shop and other warehouses."

— Andrew G. 30PW84 Customer