

DESIGNER™

Square Lay-in & Tegular
coarse texture

GREENGUARD
Gold Certified
(details below)

LEED® WELL™ | LBC

UP TO **42% RECYCLED CONTENT**

Calculate sustainability with GreenGenie™
armstrongceilings.com/greengenie

- energy management
- construction waste mgmt
- regional materials
- design for flexibility
- EPD
- recyclable/excise producer resp.
- biobased materials
- recycled content
- sourcing of raw materials
- material ingredient reporting
- low emitting materials
- lighting quality
- acoustics

LOCATION DEPENDENT

\$\$\$\$



▲ Designer™ Lay-in panels with Prelude® XL® 15/16" suspension system

Coarse-texture panels; Economical option with standard acoustical performance.

KEY SELECTION ATTRIBUTES

- Standard sound absorption
- Cost-effective

COLOR



VISUAL SELECTION

armstrongceilings.com/catdwgs	Susp. Dwg.	Item No.	Dimensions (Inches)
DESIGNER™ 15/16" Square Lay-in	1	735	24 x 24 x 5/8" □
		734	24 x 48 x 5/8" □
15/16" Angled Tegular	13	737	24 x 24 x 5/8" □


PERFORMANCE SELECTION

Dots represent high level of performance.

UL Classified Acoustics	Total Acoustics ¹	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	Durability	Recycled Content	Recycle Program	Warranty
NRC + CAC =										
0.55 30	N/A	Class A	0.81	N/A	Std	N/A	Std	Std	•	1-Yr
0.55 30	N/A	Class A	0.81	N/A	Std	N/A	Std	Std	•	1-Yr
0.55 33	N/A	Class A	0.81	N/A	Std	N/A	Std	Std	•	1-Yr

¹ Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.

SUSPENSION SYSTEMS



PHYSICAL DATA

Material
Wet-formed mineral fiber

Surface Finish
Factory-applied latex paint

Fire Performance
Class A: Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).

ASTM E1264 Classification
Type III, Form 2, Pattern F; Fire Class A

Humidity/Sag Resistance
Standard performance ceiling panels are recommended where the building is enclosed and the HVAC is continuously functioning.

VOC Emissions
GREENGUARD Gold Certified
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

Insulation Value
R Factor – 1.5 (BTU units)
R Factor – 0.26 (Watts units)

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS
UL.COM/GG
UL 2818



1-Year Limited Warranty
Details at armstrongceilings.com/warranty

Weight; Square Feet/Carton
734 – 0.80 lbs/SF; 80 SF/ctn
735, 737 – 0.80 lbs/SF; 64 SF/ctn

Minimum Order Quantity
1 carton

Metric Items Available
735M, 734M, 737M – Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.