

# AP 15

**Shurtape®**  
TRUE TO YOUR WORK™

## LABEL PROTECTION GRADE ACRYLIC PACKAGING TAPE

### TYPICAL APPLICATIONS

- For protecting shipping labels and other printed surfaces against weather and handling

### PRODUCT FEATURES

- High clarity
- Excellent tack and quick adhesion
- Non-yellowing
- UV-resistant

### CONSTRUCTION

Overall Grade/Function: Label Protection

Backing: 25 micron biaxially oriented polypropylene cast film

Adhesive: Emulsion acrylic

### STANDARD WIDTH(S)

96 mm    120 mm    144 mm

### STANDARD LENGTH(S)

66 m

Contact your Shurtape sales representative for other available sizes

### APPLICABLE STANDARDS

FDA Indirect Contact CFR 21, 175.105

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



### PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	20 lbs/in width	35.0 N/10 mm
Adhesion to Stainless Steel	19 oz/in width	2.08 N/10 mm
Thickness	1.6 mils	0.04 mm
Elongation	150%	150%
Service Temperature Range	-20 F to 180 F	-29 C to 82 C
Application Temperature Range	20 F to 110 F	-7 C to 43 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

