
APPROX WEIGHT: 28.21 lbs.

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS M-6-36 OVERALL WIDTH IS 6 5/16" OVERALL LENGTH IS 36" OVERALL HEIGHT IS 6" NUMBER OF MOUNTING HOLES 3 MOUNTING HOLE SIZE \emptyset 7/8" ACCESS HOLE SIZE \emptyset 1 3/8" (3)-REINFORCEMENT PLATES INCLUDED SIZE: 1 5/8" x 6"

DUROMETER READING: A70 ± 5

TENSIL: 1850 PSI ELONGATION: 220%

TEAR STRENGTH: 229 LBS IMPACT RESISTANCE: 75% BUMPER COLOR: BLACK

SPECIAL FEATURES

NONE

	L	DIVIDITY TOLLTANOL 1 3/4
A P P R O V		DESIGN AND DIMENSION EKNOWLEDGE MY DUTY TO EAND INSTALLATION PPLICABLE FEDERAL, STATE
A	Signed:	Date:
┕│	Printed Name:	
	LEAD TIME WILL START UPON RECEI	PT OF SIGNED APPROVAL DRAWING
DISTR	PIBLITOR'S NAME	P.O.#

		LEAD TIME WILL START OF CHARLOLIT TO GIONED ALT HOVAL DIVAVINO		
FOR INTERNAL USE ONLY		DISTRIBUTOR'S NAME:		P.O.# X
PROJECT SIGN OFF		VESTIL MANUFACTURING		W.O.# ,,
SALES				X X
ENG.		DRAWN BY: JWW	DATE: 04/25/19	SALES: X
FAB.		reference: X	SCALE: 1:3	FILE NAME:
POWER		QUOTED LEAD TIME: χ	QUOTE #	29-007-073