

Miller 210WLS-Z7 Non-Shock-Absorbing Lanyard

Description

The 210WLS-Z7 is a non-shock-absorbing web lanyard designed for positioning and restraint applications. The standard 6' model is adjustable to 4' for greater versatility. It includes 2 locking snap hooks on either end.

Materials

Webbing:	1 in. yellow nylon 1in. blue polyester (available with model 210WDLS)
Minimum Tensile:	5,000 lbs.
Thread:	Polyester thread, with a minimum tensile of 42 lbs.
Hardware:	Steel minimum tensile strength
Locking Snap Hooks:	5,000 lbs.(22kN), 3/4 in. (19mm) gate opening
<i>*All hardware meets ASTM (5) fifty-hour salt spray test requirements.</i>	
Keeper:	A black elastic keeper is used to hold the snap hook in position.

Technical

Max. Working Load: 310 lbs. - 140.62 kg

Certifications

Meets all applicable OSHA 1926.502, ANSI Z359.1, ANSI A10.32 and CSA Z259.11 requirements

Sizes Available

Available in 5 ft., 6 ft., 8 ft., 10 ft., 12 ft., 16 ft., 20 ft., 25 ft., and 30 ft. lengths.



WARNING: This product is to be used for positioning only, unless it is used in conjunction with a shock absorber.

Limitless Possibilities. Ask the Expert.

Technical Service: 800.873.5242
www.millerfallprotection.com

Honeywell Industrial Safety

900 Douglas Pike
Smithfield, RI 02917

USA

Phone: 800.430.5490
Fax: 800.322.1330

Canada

Phone: 888.212.7233
Fax: 888.667.8477

! This equipment should only be used after reading and understanding the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.