

TYPE IA

# STEPLADDER



SERIES L-3016

# 300 LBS

(Includes weight of user plus materials)

## FIBERGLASS STEPLADDER



## PRO TOP™

HOLDS ALL YOUR TOOLS  
CLOSE AT HAND

## HEAT TRANSFER TOP

No more OSHA fines due to  
missing duty rating labels.  
Scratch and UV resistant



L-3016-06



## LOUISVILLE LADDER

BECAUSE WORK AIN'T PLAY

ANSI  
Meets or exceeds requirements  
of American National Standards Institute  
ANSI A14.5



# STEPLADDER



SERIES L-3016




## 1 ProTop™

Multiple tool slots for increased productivity.



## 2 Inside Spreader Brace

Mounted inside the fiberglass rails of your ladder to help protect braces from getting hooked or damaged in transit.



## 3 Wide Back Brace

Provides maximum stability.



## 4 Boot

Slip-resistant tread.



MODEL	LADDER SIZE	MAX. REACH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WEIGHT (LBS)	APPROX. CUBES
L-3016-04	4'	8' 6"	19"	28 1/4"	14	1.8'
L-3016-06	6'	10' 4"	21 1/4"	40 3/8"	18	5.2'
L-3016-08	8'	12' 3"	24 3/4"	52 1/2"	26	8'
L-3016-10	10'	14' 2"	28"	64 3/8"	36	11.3'
L-3016-12	12'	16' 1"	31"	77"	47	15'



LOUISVILLELADDER.COM

1.800.666.2811