
ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-2-12-8

APPROX WEIGHT: 307 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

SPECIAL FEATURES

NONE

MODEL NUMBER IS AHA-2-12-8 CAPACITY IS 2,000 LBS.

BASE WIDTH IS 53 13/16" MAX OVERALL HEIGHT IS 106"

I-BEAM HEIGHT IS 8"

I-BEAM FLANGE WIDTH IS 4"

OVERALL I-BEAM LENGTH IS 144"

USABLE I-BEAM LENGTH IS 120 1/4" ADJUSTABLE UNDER I-BEAM HEIGHT

68" MIN

98" MAX

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

CASTERS: (4) Ø8" X 2" WIDE GLASS FILLED NYLON SWIVEL CASTERS WITH FOUR

LOCKING POSITIONS

CRANE MAY BE TAKEN APART AND BUNDLED WITH

(2) INCLUDED STRAPS FOR EASY TRANSPORT

ALUMINÚM CONSTRUCTION

		DIMENSION TOLERANCE ± 1/4"
F	40000	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked
	ıll	Signed: Date:

[] As drawn	[] As marked
Signed:	Date:
Printed Name:	
LEAD TIME WILL START UPON RECEI	IPT OF SIGNED APPROVAL DRAWING

LEAD TIME WILL START UP	<u>APPROVAL DRAWING</u>		
DISTRIBUTOR'S NAME:	P.O.# X		
VESTIL MANUFAC	W.O.# X		
DRAWN BY: ND	DATE: 01/	09/08	SALES: X
reference: X		SCALE: 1:29	FILE NAME:
QUOTED LEAD TIME: X	QUOTE #		28-007-189