



VELO PRO AIRMOVER

BUILT IN USA
WITH GLOBALLY SOURCED MATERIALS

FASTEST DRYING MOST PORTABLE

GOES ANYWHERE, DRIES ANYTHING!



Velo® Pro



- » *Half the size of other airmovers*
- » *Ultra-low amps*
- » *5-position versatility*

The Velo Pro's broad-path high velocity airflow drives amazing results – from an air mover that's **half the height of standard carpet dryers and draws just 1.9 amps!** With the Velo Pro, you can rapidly dry the largest area ever – or tackle special challenges with any of the unit's **five versatile positions.**




- » **DAISY CHAIN UP TO TEN UNITS PER 15-AMP CIRCUIT WITH GFCI OUTLET**
- » **LIGHT ENOUGH TO CARRY TWO OR EVEN FOUR VELOS AT ONCE** or up to six easily with a handtruck!
- » **FIVE DRYING POSITIONS** for walls, ceilings, hallways, staircases, cabinets - anywhere!
- » **COMPACT, SECURE STACKING** for storage and transport
- » **FAST CLEANING**– Remove screws and lift out impeller assembly to clean interior easily

VELO PRO	
Item #	#38MC15 - Mfr # 114969
POWER	1.2-1.9 AMPS
MOTOR	.25 HP
SPEEDS	VARIABLE SPEED
WEIGHT	18.6 LBS. 8.4 KG
DIMENSIONS (D x W x H)	24 x 18 x 9 IN.
CORD LENGTH	61 x 45.7 x 22.9 CM 18 FT. 5.5 M

«DRYING SET-UP

TEAM DEHUMIDIFIERS WITH AIRMOVERS FOR BEST RESULTS

Proper drying setup includes both the use of airmovers and dehumidifiers. Set the airmovers to create a circular airflow pattern with a dehumidifiers set in airflow path. Add the HEPA 500 if airborne contaminants are present. For areas larger than 300 sq. ft., use additional airmovers and dehumidification.



EnvironmentsHQ.com

AVAILABLE THROUGH

GRAINGER®

FOR THE ONES WHO GET IT DONE