

34 12 130 ESD


Precision Electronics Gripping Plier ESD



- for very precise assembly work, e.g. in electronics and fine mechanics
- for gripping, holding and bending
- electrically discharging handles - dissipative
- smoothly ground gripping surfaces, edges finely rounded
- approx. 20 % lighter than conventional electronics pliers
- screw joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- smooth-running double spring for a gentle and even opening
- ergonomically optimised multi- component handles
- forged from chrome vanadium ball-bearing steel
 - Style:flat, wide jaws



KNIPEX precision electronics pliers are made of high-quality ball bearing steel and processed with the highest degree of care. Each opening movement is gentle and even without backlash. Each work step proceeds reliably and precisely. This makes work much easier for professionals.




electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

Product Number	34 12 130 ESD
EAN	4003773061632
Pliers	burnished
Head	polished
Handles	with multi-component grips
Style	1
A mm	11,2
B mm	21,9
D mm	6,5
E mm	1,4
F mm	3,5
Nominal size	130 mm
Length mm	135
Net weight g	62



technical change and errors excepted

