



**Whitehall Manufacturing**<sup>®</sup>  
 Manufacturer of Healthcare and Rehabilitation Products since 1946

**BestCare**<sup>®</sup>  
 Patients, Not Prisoners<sup>®</sup>

**Healthcare and Ligature  
 Resistant Products**

Division of  
 Acorn Engineering Company<sup>®</sup>




A MEMBER OF



## Whitehall Ligature Resistant Sensor Operated Faucet

Model WH3373-WSF-SO  
 & WH3373-WSF-SO-BAT



\*\*U.S. DESIGN PATENT PENDING

WH3373-WSF-SO

Fixture May Show Some Available Options

### Ligature Resistant Sensor Operated Faucet

**The Ligature Resistant Sensor Operated Faucet** is designed and developed to retrofit existing lavatories or it can be specified for new design on decks with a thickness of 1-1/4" maximum. The Ligature Resistant Faucet is arranged to be mounted to the deck of the lavatory. Faucet assembly requires (3) 1-5/16" to 1-1/2" diameter holes on 6" or 8" centerset. Conical Faucet is chrome plated brass and provides vandal and suicide resistance.

**Valve** is a electronic valve with sensor operation. Valve includes 9VDC Sensor that will keep the solenoid open, allowing water to flow until the object is removed from sensor range. If an object is positioned in a manner that it is under constant detection the sensor will turn off the solenoid after 30-90 seconds. A 120VAC/9VDC plug-in transformer or a 6 AAA Battery Box provided.

**Optional** -MXTP Mixing Valve option is ASSE 1070 compliant and delivers tempered water flow by compensating for pressure and temperature fluctuations. Valve is to be field set to 105 Fahrenheit and includes strainers and integral checks. Operating range is 30 to 100 psi.

**Fixture is ADA Compliant.** Unit conforms with ADA requirements for accessibility when installed correctly. Compliance is subject to the interpretation and requirements of the local code authority.

### GUIDE SPECIFICATION

Provide and install Ligature Resistant Faucet Components (specify model number and options). Faucet valve shall be electronic, sensor operation. Assembly shall include 0.5 GPM flow control, 9VDC sensor and faucet connections.

Please visit [www.whitehallmfg.com](http://www.whitehallmfg.com)  
 for most current specifications.



Member of  
 U.S. Green  
 Building  
 Council



Recyclable  
 Product



Water  
 Conserving  
 Product

Complies  
 with the  
 following  
 standards:



Federal  
 Public Law  
 111-380  
 (No Lead)

Whitehall Mfg. • P.O. Box 3527 • City of Industry, CA 91744 • (800) 782-7706 • (626) 968-6681 • Fax (626) 855-4862

**WH3373-WSF-SO**

Updated: 08/04/18




**MODEL NUMBER AND OPTIONS SELECTION:**

**BASE MODEL NUMBER**

- WH3373-WSF-SO      Ligature Resistant Sensor Operated Faucet w/ Electronic Valve, Single Temp
- WH3373-WSF-SO-BAT      Ligature Resistant Battery Powered Sensor Operated Faucet w/ Electronic Valve, Single Temp


**OPTIONS:**

- WHST70-12      ASSE 1070 Compliant Hot & Cold, Temperature / Pressure Balancing Mixing Valve



**NOTES:**

1. CONICAL LIGATURE RESISTANT SPOUT
2. 9VDC INFRARED SENSOR
3. 9VDC SOLENOID VALVE ASSEMBLY
4. CHECKSTOP/STRAINER ASSEMBLY
5. 1/2" NPS INLET FLEX HOSE
6. BLANK PUSHBUTTON ESCUTCHEON ASSEMBLY
7. 9VDC PLUG-IN TRANSFORMER



**OPTIONAL -BAT BATTERY  
 OPERATION DETAIL**

**DISCLAIMER:**

This product is designed to decrease the probability that it may be utilized as an apparatus for ligature. It is not a replacement for professionals who are trained in the proper evaluation, management and supervision of persons at risk of suicide.

**⚠ WARNING: Cancer and Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)**

**SELECTION SUMMARY & APPROVAL FOR MANUFACTURING**

Model Number & Options \_\_\_\_\_ Quantity \_\_\_\_\_  
 Company \_\_\_\_\_ Date \_\_\_\_\_  
 Contact \_\_\_\_\_ Title \_\_\_\_\_  
 Approval for Manufacturing/Signature \_\_\_\_\_

All dimensions are nominal and subject to manufacturer's change without notice. Whitehall assumes no responsibility for use of void or superseded data. Whitehall Manufacturing, Member of Morris Group International. Please visit [www.whitehallmfg.com](http://www.whitehallmfg.com) for most current specifications.